

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet, 2x2xAWG26/7, S/UTP, gray

## Your advantages

- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- High-speed data transmission with up to 1 Gbps (CAT5)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1227562       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB11          |
| Product key                          | ABNABG        |
| GTIN                                 | 4063151322007 |
| Weight per piece (including packing) | 105.666 g     |
| Weight per piece (excluding packing) | 105.666 g     |
| Customs tariff number                | 85444290      |
| Country of origin                    | CN            |

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Product family      | RJ45 STANDARD CAT5      |
| Sensor type         | Ethernet                |
| Number of positions | 8                       |
| Shielded            | yes                     |
| Cable outlet        | straight                |

### Insulation characteristics

|                      |   |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution  | 2 |

### Electrical properties

|   |        |
|---|--------|
| Rated voltage (III/2)                   | 72 V   |
| Transmission medium                     | Copper |
| Transmission characteristics (category) | CAT5   |
| Power transmission                      | PoE++  |

### Mechanical properties

#### Mechanical data

|                                     |         |
|-------------------------------------|---------|
| Insertion force per signal contact  | 30.00 N |
| Extraction force per signal contact | 50 N    |

### Material specifications

|  |       |
|--|-------|
| Flammability rating according to UL 94 | V0    |
| Contact material                       | Brass |
| Contact surface material               | Au    |
| Contact carrier material               | PC    |
| Outer sheath, material                 | LSZH  |

### Dimensions

|        |         |
|--------|---------|
| Width  | 11.6 mm |
| Height | 14.8 mm |
| Length | 40 mm   |

### Connection data

#### Connection technology

|                   |                   |
|-------------------|-------------------|
| Connection method | Pierce connection |
|-------------------|-------------------|

#### Conductor connection

|                   |                   |
|-------------------|-------------------|
| Connection method | Pierce connection |
|-------------------|-------------------|

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

## Connector

### Connection 1

|                                 |                    |
|---------------------------------|--------------------|
| Type                            | Plug straight RJ45 |
| Shielded                        | yes                |
| Handle color                    | gray               |
| Insertion/withdrawal cycles     | ≥ 750              |
| Degree of protection            | IP20               |
| Ambient temperature (operation) | -20 °C ... 80 °C   |

### Connection 2

|                                 |                    |
|---------------------------------|--------------------|
| Type                            | Plug straight RJ45 |
| Shielded                        | yes                |
| Handle color                    | gray               |
| Insertion/withdrawal cycles     | ≥ 750              |
| Degree of protection            | IP20               |
| Ambient temperature (operation) | -20 °C ... 80 °C   |

## Cable/line

|              |        |
|--------------|--------|
| Cable length | 2.00 m |
|--------------|--------|

### Ethernet, Type B, 8-pos., CAT5, LSZH [BC5]

|   |  |
|---|--|
| Number of positions                         | 8  |
| Shielded                                    | yes  |
| Cable type                                  | Ethernet, Type B, 8-pos., CAT5, LSZH [BC5] |
| Conductor structure                         | 2x2xAWG26/7, S/UTP                         |
| Conductor structure signal line             | 7x 0.16 mm                                 |
| AWG signal line                             | 26   |
| Wire diameter incl. insulation              | 0.85 mm                                    |
| External cable diameter                     | 5.70 mm ±0.3 mm                            |
| Outer sheath, material                      | LSZH                                       |
| External sheath, color                      | gray                                       |
| Conductor material                          | Bare Cu litz wires                         |
| Material wire insulation                    | PE   |
| Single wires, quantity                      | 8  |
| Single wire, cross section [AWG]            | 26   |
| Thickness, outer sheath                     | approx. 0.70 mm                            |
| Optical shield covering                     | 70 %                                       |
| Insulation resistance                       | ≥ 5000 MΩ*km                               |
| Loop resistance                             | ≤ 148.00 Ω/km                              |
| Wave impedance                              | 100 Ω                                      |
| Minimum bending radius, fixed installation  | 8 x D                                      |
| Smallest bending radius, fixed installation | 46 mm                                      |
| Near end crosstalk attenuation (NEXT)       | 65.3 dB (with 1 MHz)                       |
|   | 56.3 dB (at 4 MHz)                         |

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

|  |   |
|--|---|
|  | 50.3 dB (at 10 MHz)                             |
|  | 47.2 dB (at 16 MHz)                             |
|  | 45.8 dB (at 20 MHz)                             |
|  | 42.9 dB (at 31.25 MHz)                          |
|  | 38.4 dB (at 62.5 MHz)                           |
|  | 35.3 dB (at 100 MHz)                            |
| Power-summed near end crosstalk attenuation (PSNEXT) | 62.3 dB (with 1 MHz)                            |
|  | 53.3 dB (at 4 MHz)                              |
|  | 48.8 dB (at 8 MHz)                              |
|  | 47.3 dB (at 10 MHz)                             |
|  | 44.2 dB (at 16 MHz)                             |
|  | 42.8 dB (at 20 MHz)                             |
|  | 41.3 dB (at 25 MHz)                             |
|  | 39.9 dB (at 31.25 MHz)                          |
|  | 35.4 dB (at 62.5 MHz)                           |
|  | 32.3 dB (at 100 MHz)                            |
| Return attenuation (RL)                              | 20 dB (with 1 MHz)                              |
|  | 23 dB (at 4 MHz)                                |
|  | 24.5 dB (at 8 MHz)                              |
|  | 25 dB (at 10 MHz)                               |
|  | 25 dB (at 16 MHz)                               |
|  | 25 dB (at 20 MHz)                               |
|  | 24.2 dB (at 25 MHz)                             |
|  | 23.3 dB (at 31.25 MHz)                          |
|  | 20.7 dB (at 62.5 MHz)                           |
|  | 19 dB (at 100 MHz)                              |
| Shield attenuation                                   | 3.2 dB (with 1 MHz)                             |
|  | 6.01 dB (at 4 MHz)                              |
|  | 9.49 dB (at 10 MHz)                             |
|  | 12.07 dB (at 16 MHz)                            |
|  | 13.54 dB (at 20 MHz)                            |
|  | 17.11 dB (at 31.25 MHz)                         |
|  | 24.76 dB (at 62.5 MHz)                          |
|  | 31.99 dB (at 100 MHz)                           |
| Halogen-free   | complying with IEC 60754-1/2                    |
| Flame resistance                                     | IEC 60332-1-2/IEC 60332-3-24/CM                 |
| Ambient temperature (operation)                      | -20 °C ... 80 °C (cable, fixed installation)    |
|  | -20 °C ... 80 °C (Cable, flexible installation) |
| Ambient temperature (installation)                   | 0 °C ... 60 °C                                  |

## Environmental and real-life conditions

Ambient conditions

Degree of protection

IP20

# NBC-R4OC/2,0-BC5/R4OC - Patch cable

1227562

<https://www.phoenixcontact.com/us/products/1227562>



|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -20 °C ... 80 °C |
| Ambient temperature (storage/transport) | 0 °C ... 40 °C   |

## Standards and regulations

|                  |               |
|------------------|---------------|
| Flame resistance | IEC 60332-1-2 |
|------------------|---------------|

# NBC-R4OC/2,0-BC5/R4OC - Patch cable

1227562

<https://www.phoenixcontact.com/us/products/1227562>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1227562>



**EAC**

Approval ID: 19060508



**UL Listed**

Approval ID: E335024\_20210804



**cUL Listed**

Approval ID: E335024\_20210804

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# NBC-R4OC/2,0-BC5/R4OC - Patch cable



1227562

<https://www.phoenixcontact.com/us/products/1227562>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)