

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Data connector, PROFIBUS, INTERBUS, 5-position, shielded, Socket straight M12, coding: B, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg11, external cable diameter 8 mm ... 10 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1401097 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF30 |
| Product key | AF2CBA |
| GTIN | 4046356523356 |
| Weight per piece (including packing) | 57.64 g |
| Weight per piece (excluding packing) | 57.64 g |
| Customs tariff number | 85366990 |
| Country of origin | HU |

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Application | Data |
| Sensor type | PROFIBUS |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | B |
| Cable outlet | straight |
| Pg screw connection | Pg11 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Dimensions

| | |
|------------------------|---------|
| Dimensional drawing | |
| Width | 20.2 mm |
| Height | 20.2 mm |
| Length | 57 mm |
| Wrench size, union nut | 16 mm |

External dimensions

| | |
|------------------|----------------|
| Outside diameter | 8 mm ... 10 mm |
|------------------|----------------|

Housing

| | |
|------------------|---------|
| Diameter housing | 20.2 mm |
|------------------|---------|

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Material of grip body | Zinc die-cast, nickel-plated |
| Contact material | CuZn |

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

| | |
|-------------------------------|------------------------------|
| Contact surface material | Au |
| Contact carrier material | PA |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connection data

Conductor connection

| | |
|---|--|
| Connection method | Screw connection |
| Connection cross section | 0.25 mm ² ... 0.75 mm ² (without ferrule) 0.14 mm ² ... 0.75 mm ² (with ferrule) 0.25 mm ² ... 0.75 mm ² (solid) |
| Connection cross section AWG | 24 ... 18 (without ferrule) 26 ... 20 (with ferrule) |
| Stripping length of the individual wire | 5 mm |
| Tightening torque | 0.4 Nm (M12 knurl) 0.2 Nm (Screw terminal blocks) 1 Nm ... 1.4 Nm (Pressure nut with 8 mm ... 12 mm external cable diameter) |

Electrical properties

| | |
|--------------------------------|--------------------|
| Rated surge voltage | 1.5 kV |
| Contact resistance | ≤ 3 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 48 V AC 60 V DC |
| Nominal current I _N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | B |

Cable/line

| | |
|---|----------------------|
| Signal type/category | PROFIBUS INTERBUS |
| Stripping length of the individual wire | 5 mm |

Environmental and real-life conditions

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector




1401097

<https://www.phoenixcontact.com/us/products/1401097>

Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector




1401097


<https://www.phoenixcontact.com/us/products/1401097>

Functional drawing


Assembly steps for M 12 male/female connector and conductor



Slide parts onto the conductor



Strip conductor, widen shield and lay around the shielding ring, cut off projecting mesh.




SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097


<https://www.phoenixcontact.com/us/products/1401097>

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

Schematic diagram



Cable connection side M12 (screw connection)

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1401097>

| | | cUL Recognized | | | |
|-------|--|----------------------------|-----------------------|-----------------------|-------------------|
| | | Approval ID: FILE E 221474 | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| keine | | 60 V | 4 A | - | - |

| | | UL Recognized | | | |
|-------|--|----------------------------|-----------------------|-----------------------|-------------------|
| | | Approval ID: FILE E 221474 | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| keine | | 60 V | 4 A | - | - |

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-M12FSB-5CON-PG9 SH XL PB - Data connector



1401097

<https://www.phoenixcontact.com/us/products/1401097>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 15b3584c-1863-48e0-85e8-197fb9a28fd3 |

EF3.0 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.991 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com