

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Splice box, design: 19" rack patch module, degree of protection: IP20, material: Sheet steel, connection method: Splicing, color: light grey RAL 7035, Ethernet



Product description

19" FDX 20 series splice boxes, 1 RU, with removable drawer, for 24x LC duplex OM2, gray, completely ready to splice (correctly pre-mounted: 24 ceramic couplings, 48 pigtailed, 4 cassettes, 8 combs, 1 cassette cover, and 48x shrink splice protectors).
4 cable entries (rear) incl. 4 M20 cable glands, measurement protocol and 19" mounting set.

Commercial data

Item number	1418816
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB15
Product key	ABNGBA
GTIN	4055626151700
Weight per piece (including packing)	4,221 g
Weight per piece (excluding packing)	4,221 g
Customs tariff number	85389099
Country of origin	DE

FOC-SB-FRAME-19-LC:24-OM2 GY - Splice box

1418816

<https://www.phoenixcontact.com/us/products/1418816>



Technical data

Product properties

Product type	Network distributor box
Housing type	Component housing
Type	1RU
Sensor type	Ethernet
Connection profile	LC connectors
No. of cable outlets	4
No. of conductors	48
Number of module slots	24
Number of slots	48
Protective cover	yes

Electrical properties

Attenuation	>= 0.3 dB
-------------	-----------

Connection data

Connection technology	
Connection method	Splicing

Dimensions

Dimensional drawing	
Width	483 mm
Height	43.8 mm
Depth	329 mm
Drill hole distance, horizontal	31.75 mm

Housing	
Housing width	441 mm

Mechanical characteristics	
Ferrule diameter	1.25 mm

Material specifications

Color	light grey RAL 7035
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics

FOC-SB-FRAME-19-LC:24-OM2 GY - Splice box

1418816

<https://www.phoenixcontact.com/us/products/1418816>



Housing material	Sheet steel
Housing surface material	Powder-coated, gray

Cable/line

Cable type	Fiberglass
Cable type	for all common cable types
Cable structure	semi-loose compact wires (STB)
Individual wire diameter	900 µm (250/900 µm)
Single wire, color	color coded
Whip length	750 mm

FO cable

Number of fibers	48
Fiber	GOF
Fiber type	Multimode fiberglass 50/125 µm
Attenuation	≤ 0.3 dBc (with 850 nm)
Transmission medium	FO

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	min. 1000

Characteristics

Attenuation	>= 0.3 dB
-------------	-----------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

FOC-SB-FRAME-19-LC:24-OM2 GY - Splice box




1418816

<https://www.phoenixcontact.com/us/products/1418816>

Drawings

Dimensional drawing



Classifications

UNSPSC

UNSPSC 21.0

39121421

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com