

SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 4-position, PUR halogen-free, orange RAL 2003, shielded (Advanced Shielding Technology), Plug straight M12, coding: S, on Socket straight M12, coding: S, cable length: 3 m, for AC current up to 12 A/690 V

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special S-coding
- Shield power reliably – 360° shielding to reduce electromagnetic loads
- Our standard: robust halogen-free PUR cable

Commercial data

Item number	1423650
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF05
Product key	AF1CCP
GTIN	4055626353029
Weight per piece (including packing)	480 g
Weight per piece (excluding packing)	478 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

Technical data

Product properties

Product type	Power cable
Application	Energy supply
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	S

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	PP
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	690 V AC
Nominal current I_N	12 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Type	Plug straight M12
Coding type	S (Power)

Connection 2

Type	Socket straight M12
Coding type	S (Power)

Cable/line

Cable length	3 m
--------------	-----

PUR halogen-free orange shielded [PUR]

SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

UL AWM Style	80°C/1000 V
Number of positions	4
Shielded	yes
Cable type	PUR halogen-free orange shielded [PUR]
Conductor structure, voltage supply	44x 0.20 mm
AWG power supply	16
Conductor cross section	4x 1.5 mm²
Wire diameter incl. insulation	≤ 2.35 mm
External cable diameter	8.20 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, black 3, green/yellow
Thickness, insulation	0.36 mm
Thickness, outer sheath	0.90 mm
Overall twist	4 wires optimally twisted
Max. conductor resistance	≤ 14.1 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	1000 V AC
Test voltage	≥ 10000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥500000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	According to DIN EN 60332-2-2 (20 s) UL 1581, FT2
Resistance to oil	according to DIN EN 60811-404, 168 h at 100 °C
Other resistance	UV resistant Low adhesion
Ambient temperature (operation)	-50 °C ... 80 °C (cable, fixed installation) -30 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67 (without preloading, as additional test in accordance with IEC 60529)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

1423650

<https://www.phoenixcontact.com/us/products/1423650>

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight

1423650


<https://www.phoenixcontact.com/us/products/1423650>

Schematic diagram



M12 plug pin assignment, 4-pos., S-coded, plug side view

Schematic diagram



Pin assignment of M12 socket, 4-pos., S-coded, socket side view


SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

Circuit diagram



Contact assignment of the M12 plug

1423650
<https://www.phoenixcontact.com/us/products/1423650>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1423650>

 UL Listed Approval ID: FILE E 468743				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	600 V	12 A	- 16	- 16

 cUL Listed Approval ID: FILE E 468743				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	600 V	12 A	- 16	-

SAC-4P-M12MSS/3,0-PUR/FSSPESH - Power cable



1423650

<https://www.phoenixcontact.com/us/products/1423650>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%