

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact carrier, 8-position, Pin, straight, M12, A-coding, Crimp connection, 0.25 mm<sup>2</sup>



## Your advantages

- Convenient field assembly: device connectors for fast on-site mounting
- Contact carriers that are designed for assembly or available with preassembled litz wires
- Standard pin assignments for signal and power transmission with a uniform design-in design

## Commercial data

Item number	1440928
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB24
Product key	ABQCED
GTIN	4046356533768
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	0.73 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Number of positions	8
No. of cable outlets	1
Seal present	no
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V
Nominal current $I_N$	2 A

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Signaling

Status display	no
Status display present	no

### Material specifications

Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

### Connector

Connection 1
--------------

# SACC-MCI-M12MS-8CON - Contact carrier

1440928

<https://www.phoenixcontact.com/us/products/1440928>



Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

## Cable/line

Cable cross section	0.25 mm <sup>2</sup>
---------------------	----------------------

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
Ambient temperature (operation) (fixed installation)	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

## Mounting

Mounting type	Front/square flange mounting (25 mm side length)
---------------	--

# SACC-MCI-M12MS-8CON - Contact carrier


1440928

<https://www.phoenixcontact.com/us/products/1440928>




## Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

Circuit diagram



Contact assignment of the M12 plug

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)