

# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled D-SUB cable shielded, 25-pos., stranded (7-wire), cable color RAL 7000 (gray), IP20 degree of protection, head 1 with socket shell 3 and straight cable outlet, head 2 with pin shell 3 and straight cable outlet, length: 5 m

## Commercial data

Item number	1656314
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAS
GTIN	4046356029797
Weight per piece (including packing)	426.1 g
Weight per piece (excluding packing)	417.6 g
Customs tariff number	85444290
Country of origin	CN

1656314

<https://www.phoenixcontact.com/us/products/1656314>

## Technical data

### Product properties

Product type	Data cable preassembled
Type	D-SUB
Sensor type	Universal
Number of positions	25
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated current	1 A
Operating voltage	30 V
Transmission medium	Copper

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

### Material specifications

Housing material	PVC
Contact material	Copper alloy
Contact surface material	gold-plated
Outer sheath, material	PVC

### Connection data

#### Connection technology

Connection method	D-SUB
-------------------	-------

#### Conductor connection

Connection method	D-SUB
-------------------	-------

### Connector

#### Connection 1

Type	Socket straight D-SUB 25
Degree of protection	IP20

#### Connection 2

Type	Plug straight D-SUB 25
Degree of protection	IP20

# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

## Cable/line

Outer sheath, material	PVC
Cable cross section	0.08 mm <sup>2</sup>
Conductor structure signal line	7.00 mm
AWG signal line	28

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	0 °C ... 70 °C


# VS-25-DSUB-20-LI-5,0 - D-SUB cable

1656314

<https://www.phoenixcontact.com/us/products/1656314>


## Drawings

Schematic diagram



Connector pin assignment

Schematic diagram



Pin connector pattern


# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

Circuit diagram



Circuit diagram

# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1656314>



**EAC**

Approval ID: 19060508

# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27440322

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-25-DSUB-20-LI-5,0 - D-SUB cable



1656314

<https://www.phoenixcontact.com/us/products/1656314>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)