

VS-PN-CABLE-1021/PVC-5X1,5/100 - Power cable



1659007

<https://www.phoenixcontact.com/us/products/1659007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power cable, number of positions: 5, PROFINET/power



Commercial data

Item number	1659007
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNOIA
GTIN	4046356182010
Weight per piece (including packing)	12,808 g
Weight per piece (excluding packing)	12,800 g
Country of origin	DE

VS-PN-CABLE-1021/PVC-5X1,5/100 - Power cable

1659007

<https://www.phoenixcontact.com/us/products/1659007>



Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data cable by the meter
Sensor type	PROFINET/power
Number of positions	5
Shielded	no

Electrical properties

Rated voltage (III/3)	500 V
-----------------------	-------

Material specifications

Outer sheath, material	PVC
Conductor material	Bare Cu litz wires

Cable/line

PVC gray [PVC]	
Shielded	no
Cable type	PVC gray
Cable type (abbreviation)	PVC
External cable diameter	8.1 mm
Outer sheath, material	PVC
External sheath, color	silver-grey RAL 7001
Conductor material	Bare Cu litz wires
Conductor cross section	1.5 mm ²
Smallest bending radius, fixed installation	40 mm
Smallest bending radius, movable installation	150 mm

FO cable	
Transmission medium	Copper

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 70 °C (Cable, flexible installation)

VS-PN-CABLE-1021/PVC-5X1,5/100 - Power cable

1659007

<https://www.phoenixcontact.com/us/products/1659007>



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com