

FB-PS-MB-25DSUB/EX - Power supply unit

2316146

<https://www.phoenixcontact.com/us/products/2316146>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Four-channel, redundant fieldbus power supply base. Host connection is a D-SUB 25 socket connector.



Product description

Universal four-channel, redundant fieldbus power supply base with D-SUB 25 host connector.

Your advantages

- Redundancy
- Built-in relay diagnostics

Commercial data

Item number	2316146
Packing unit	1 pc
Sales key	DN11
Product key	DNC1Z1
GTIN	4055626128351
Weight per piece (including packing)	1,078.6 g
Weight per piece (excluding packing)	1,131 g
Customs tariff number	85366990
Country of origin	US

FB-PS-MB-25DSUB/EX - Power supply unit

2316146

<https://www.phoenixcontact.com/us/products/2316146>



Technical data

Notes

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Product properties

Product type	Device coupler
--------------	----------------

Output data

Signal	
Output name	Alarm

Connection data

Supply	
Conductor cross-section, flexible	0.20 mm ² ... 2.50 mm ²
Conductor cross-section, rigid	0.20 mm ² ... 2.50 mm ²
Conductor cross-section AWG	30 ... 12

Ex data

Safety data	
Inductance Li	17.8 mH (trunk and host)
Max. output voltage U _o	30 V DC (trunk and host)

Interfaces

Data: Invensys DCS cabling system	
Number of connections	1
Connection method	D-SUB-25 female connector

Dimensions

Width	180 mm
Height	77 mm
Depth	180 mm

Mechanical tests

Corrosive resistance in accordance with ANSI-ISA 71.04-1985 -	:
Severity level G3	

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

FB-PS-MB-25DSUB/EX - Power supply unit

2316146

<https://www.phoenixcontact.com/us/products/2316146>



Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)
Permissible humidity (operation)	95 % (non-condensing)

Approvals

Conformity/Approvals

Conformance	CE-compliant
Fieldbus Foundation	FF-831
EN	EN 61326
NE	NAMUR NE 21

Ex data

ATEX	Sira 11ATEX4216X; II 3 G Ex nA nC IIC T4 Gc
IECEx	IECEx SIR 11.0097X; Ex nA nC IIC T4 Gc
CSA, USA/Canada	Class I, Div. 2, Groups A, B, C, D; Ex nA nC IIC T4 Class I, Zone 2, AEx nA nC IIC T4

Standards and regulations

Standards

Standards/regulations	NE21
	EN 61326

Standards/regulations

Standards/regulations	Ring wave noise immunity in acc. with IEC 61000-4-12
-----------------------	--

Standards/regulations

Standards/regulations	Dry heat in acc. with IEC 61131-2
-----------------------	-----------------------------------

Standards/regulations

Standards/regulations	Damp heat in acc. with IEC 61131-2
-----------------------	------------------------------------

Standards/regulations

Standards/regulations	Shock and vibration in acc. with EN 61131-2 and EN 50178
Standards/regulations	IEC 61158-2

FB-PS-MB-25DSUB/EX - Power supply unit

2316146

<https://www.phoenixcontact.com/us/products/2316146>



Classifications

ECLASS

ECLASS-13.0	27242692
-------------	----------

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FB-PS-MB-25DSUB/EX - Power supply unit

2316146

<https://www.phoenixcontact.com/us/products/2316146>



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com