

IBS RL 24 DIO 4/2/4-LK-2MBD - Distributed I/O device



2732486

<https://www.phoenixcontact.com/us/products/2732486>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital I/O device for INTERBUS; fiber optic technology with 2 Mbaud, four inputs (24 V DC), two outputs (24 V DC, 0.5 A), sensor/actuator connection via 5-pos. M12 female connectors, rugged metal housing, IP67 protection

Your advantages

- Rugged metal housing
- Comprehensive diagnostic functions
- M12 connector for I/O devices
- Rugged Line connector for INTERBUS, either with fiber optic or twisted pair, and supply voltage

Commercial data

Item number	2732486
Packing unit	1 pc
Sales key	DR03
Product key	DRI513
GTIN	4017918187118
Weight per piece (including packing)	707.5 g
Weight per piece (excluding packing)	650 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Dimensions

Width	127 mm
Height	67 mm
Depth	71 mm
Note on dimensions	with bus connection plugs and mounting panel

Interfaces

INTERBUS

Connection method	Optic fiber (polymer fiber 980/1000 µm)
Transmission speed	2 Mbps
Transmission physics	FO

Input data

Digital:

Input name	Digital inputs
Number of inputs	4
Connection technology	2-, 3-, 4-conductor
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Total sensor current	max. 200 mA
Typical input current per channel	3 mA
Delay at signal change from 0 to 1	3 ms
Delay at signal change from 1 to 0	3 ms
Protective circuit	Electronic short-circuit/overload protection for each group

Output data

Digital:

Output name	Digital outputs
Connection technology	2-, 3-conductor
Number of outputs	2
Protective circuit	Electronic short-circuit/overload protection for each channel; Freewheeling diode
Output voltage	24 V DC
Maximum output current per channel	500 mA
Nominal output voltage	24 V
Output voltage when switched off	max. 1 V
Output current when switched off	max. 100 µA
Nominal load, inductive	12 VA (1.2 H, 48 Ω)
Nominal load, lamp	12 W
Nominal load, ohmic	12 W

Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Overcurrent shut-down	min. 0.7 A
Output current with ground connection interrupt when switched off	max. 25 mA

Product properties

Product type	I/O component
Product family	Ruggedline
Type	Block design
No. of channels	6

Electrical properties

Supply: Module electronics

Supply voltage	24 V DC
Supply voltage range	18.5 V DC ... 32 V DC (including ripple)
Supply current	typ. 80 mA (plus sensor current)
Ripple	Max 3.6 V _{SS} within the permissible voltage range

Electrical isolation/isolation of the voltage ranges

Test voltage: Between bus logic and outputs	500 V AC, 50 Hz, 1 min
---	------------------------

Connection data

Connection method	Fiber optic
-------------------	-------------

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	0 °C ... 55 °C
Degree of protection	IP65/IP67
Note	Seal unused slots/connections to ensure the degree of protection.
Air pressure (operation)	860 hPa ... 1080 hPa (up to 1500 m above sea level)
Air pressure (storage/transport)	660 hPa ... 1080 hPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	100 %
Permissible humidity (storage/transport)	95 % (non-condensing)

Mounting

Mounting type	Panel mounting
---------------	----------------

Drawings

Connection diagram



IBS RL 24 DIO 4/2/4-LK-2MBD - Distributed I/O device



2732486

<https://www.phoenixcontact.com/us/products/2732486>

Classifications

ETIM

ETIM 8.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------