

FLKM-PA-2D15/HW/DO/C300 - Front adapter

2900924

<https://www.phoenixcontact.com/us/products/2900924>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Honeywell C300, Series C I/O. Specifically for connecting PLC-V8/D15.../OUT. Transmission of 2x 8 channels.

Your advantages

- Front adapter with two 15-pos. D-SUB connectors
- Specifically for connecting PLC-V8/D15.../OUT
- Preassembled system cables are connected directly to I/O modules using the front adapters

Commercial data

Item number	2900924
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK231H
GTIN	4046356551182
Weight per piece (including packing)	91.4 g
Weight per piece (excluding packing)	99.8 g
Customs tariff number	85366990
Country of origin	DE

FLKM-PA-2D15/HW/DO/C300 - Front adapter

2900924

<https://www.phoenixcontact.com/us/products/2900924>



Technical data

Product properties

Product type	Front adapter
Product family	VARIOFACE

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Oversupply category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

Supported controller HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDOB01 (non-redundant)
	TDOB11 (redundant)

Connection data

Connection 1 (control level)

Connection method	Plug-in connection
Number of connections	2
Number of positions	16
Pitch	5.08 mm

Connection 2 (field level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	2
Number of positions	15
Insertion/withdrawal cycles	> 500
Pitch	2.74 mm

Connection 3 (shield)

Connection method	Spade connection
Number of positions	1
Note	2,8 x 0,8

FLKM-PA-2D15/HW/DO/C300 - Front adapter

2900924

<https://www.phoenixcontact.com/us/products/2900924>



Dimensions

Item dimensions

Width	93.8 mm
Height	28 mm
Depth	47.04 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	Plug-in mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-PA-2D15/HW/DO/C300 - Front adapter


2900924

<https://www.phoenixcontact.com/us/products/2900924>



Drawings

Circuit diagram



Connection scheme: FLKM-PA-2D15/HW/DO/C300

FLKM-PA-2D15/HW/DO/C300 - Front adapter

2900924

<https://www.phoenixcontact.com/us/products/2900924>



Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FLKM-PA-2D15/HW/DO/C300 - Front adapter

2900924

<https://www.phoenixcontact.com/us/products/2900924>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com