

RAD-TAPE-SV-19-3 - Weather protection tape

2903182

<https://www.phoenixcontact.com/us/products/2903182>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Vulcanizing sealing tape for external protection of adapters, cable connections, etc. against the effects of weather, roll length: 3 m



Your advantages

- Vulcanizing
- Provides additional weather protection for adapters, splitters, cable connections, etc.

Commercial data

Item number	2903182
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356723664
Weight per piece (including packing)	59.7 g
Weight per piece (excluding packing)	51.5 g
Customs tariff number	59061000
Country of origin	TW

RAD-TAPE-SV-19-3 - Weather protection tape

2903182

<https://www.phoenixcontact.com/us/products/2903182>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Mounting material
Features	Self-vulcanizing

Dimensions

Width	19 mm
Length	3 m

Material specifications

Color	black (RAL 9005)
Material	Polyisobutylene

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (storage/transport)	10 °C ... 30 °C

Mounting

Assembly note	Outdoor installation
---------------	----------------------

RAD-TAPE-SV-19-3 - Weather protection tape

2903182

<https://www.phoenixcontact.com/us/products/2903182>



Classifications

ECLASS

ECLASS-13.0	27140708
ECLASS-15.0	27140708

ETIM

ETIM 9.0	EC000128
----------	----------

UNSPSC

UNSPSC 21.0	44121600
-------------	----------

RAD-TAPE-SV-19-3 - Weather protection tape

2903182

<https://www.phoenixcontact.com/us/products/2903182>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com