

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module, with push-in connection for 8 channels



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2903801 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C423 |
| Product key | DK2121 |
| GTIN | 4046356796750 |
| Weight per piece (including packing) | 78.5 g |
| Weight per piece (excluding packing) | 98 g |
| Customs tariff number | 85366990 |
| Country of origin | US |

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Technical data

Product properties

| | |
|---------------------|------------------------|
| Product type | Interface module |
| Product family | VARIOFACE Professional |
| Number of positions | 14 |
| No. of channels | 8 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|---------|
| Max. permissible operating voltage | 25 V AC |
| | 60 V DC |
| Max. current carrying capacity per branch | 1 A |
| Max. total current of voltage supply | 3 A |
| Rated surge voltage | 0.6 kV |

Supported controller SIEMENS S7-1500

| | |
|-------------------|---|
| Suitable I/O card | 6ES7521-1BH00-0AB0 |
| | 6ES7521-1BH10-0AA0 |
| | 6ES7521-1BH50-0AA0 |
| | 6ES7521-1BL00-0AB0 |
| | 6ES7521-1BL10-0AA0 |
| | 6ES7521-1BP00-0AA0 (Sinking mode) |
| | 6ES7522-1BH00-0AB0 |
| | 6ES7522-1BH01-0AB0 |
| | 6ES7522-1BL00-0AB0 |
| | 6ES7522-1BL01-0AB0 |
| | 6ES7522-1BL10-0AA0 |
| | 6ES7522-1BP00-0AA0 |
| | 6ES7522-1BP50-0AA0 |
| | 6ES7523-1BL00-0AA0 |
| | 6ES7523-1BP50-0AA0 (DI32 (Sinking mode)/DQ32) |

Supported controller ALLEN-BRADLEY ControlLogix

| | |
|-------------------|------------|
| Suitable I/O card | 1756-IB32 |
| | 1756-OB32 |
| | 1756-IN16 |
| | 1756-IB16 |
| | 1756-IC16 |
| | 1756-OB16E |

Supported controller ABB S800 I/O

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

| | |
|-------------------|-------|
| Suitable I/O card | DI810 |
| | DI811 |
| | DI830 |
| | DI831 |
| | DI840 |
| | DO810 |
| | DO814 |
| | DO818 |
| | DO840 |

Supported controller GE-FANUC RX3i

| | |
|-------------------|-------------|
| Suitable I/O card | IC694MDL754 |
| | IC694MDL660 |

Supported controller HONEYWELL Experion PKS C200

| | |
|-------------------|------------|
| Suitable I/O card | TC-IDD 321 |
| | TC-ODD 321 |

Supported controller MITSUBISHI MELSEC L

| | |
|-------------------|----------|
| Suitable I/O card | LX41C4 |
| | LX42C4 |
| | LY41NT1P |
| | LY42NT1P |
| | LY41PT1P |
| | LY42PT1P |

Supported controller MITSUBISHI MELSEC Q

| | |
|-------------------|---------|
| Suitable I/O card | QX81 |
| | QY81P |
| | QX41 |
| | QX41-S1 |
| | QX42 |
| | QX42-S1 |
| | QX71 |
| | QX72 |
| | QY41P |
| | QY42P |
| | QY71 |
| | QH42P |
| | QX82 |
| | QX82-S1 |
| | QY82P |

Supported controller SCHNEIDER ELECTRIC Modicon TSX QUANTUM

| | |
|-------------------|---------|
| Suitable I/O card | DDI 353 |
| | DDI 853 |

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

| | |
|--|---------|
| | DAI 453 |
| | DDO 353 |

Connection data

Field level

| | |
|----------------------------------|--|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 26 ... 14 |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 14 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 41.9 mm |
| Height | 72.1 mm |
| Depth | 56 mm |

Material specifications

| | |
|--|-----------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Housing insulation material | Polyamide PA non-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Notes

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

VIP-2/PT/FLK14/PLC - Passive module




2903801

<https://www.phoenixcontact.com/us/products/2903801>

Drawings

Circuit diagram



VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903801>

|  CSA Approval ID: 2122203 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

|  cUL Recognized Approval ID: E238705 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

|  UL Recognized Approval ID: E238705 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

|  CSAus Approval ID: 2122203 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002780 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VIP-2/PT/FLK14/PLC - Passive module



2903801

<https://www.phoenixcontact.com/us/products/2903801>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com