

UM-2KS50/DO 4/RS/K/SO225 - Output module



2904111

<https://www.phoenixcontact.com/us/products/2904111>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



4-channel digital output module with screw connection. The voltage supply and the 50-pos. strip are designed redundantly. Suitable for the Yokogawa SDV 521 card.

Commercial data

Item number	2904111
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK2A81
GTIN	4046356783750
Weight per piece (including packing)	599 g
Weight per piece (excluding packing)	599 g
Country of origin	DE

UM-2KS50/DO 4/RS/K/SO225 - Output module



2904111

<https://www.phoenixcontact.com/us/products/2904111>

Technical data

Product properties

Product type	Interface module
No. of channels	4

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC (Permissible range: 19 V - 30 V DC)
Max. current carrying capacity per branch	2 A (slow-blow)
Max. total current of all branches	10 A (slow-blow)

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μ s)

Supported controller YOKOGAWA ProSafe-RS

Suitable I/O card	SDV521
-------------------	--------

Connection data

Field level

Connection method	Screw connection
Number of positions	8
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Tightening torque	0.5 Nm

Supply

Connection method	Screw/plug-in connection
Conductor cross-section rigid	0.34 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Signaling

Status display present	yes
------------------------	-----

UM-2KS50/DO 4/RS/K/SO225 - Output module



2904111

<https://www.phoenixcontact.com/us/products/2904111>

Dimensions

Item dimensions

Width	145.1 mm
Height	111.8 mm
Depth	93.3 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	< 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UM-2KS50/DO 4/RS/K/SO225 - Output module



2904111

<https://www.phoenixcontact.com/us/products/2904111>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UM-2KS50/DO 4/RS/K/SO225 - Output module



2904111

<https://www.phoenixcontact.com/us/products/2904111>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com