

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module

2972699

<https://www.phoenixcontact.com/us/products/2972699>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Interface module, with plug-in socket for 8 solid-state relays, with security latch, with screw connection, with light indicator and fuse, control logic: plus switching



Your advantages

- Status indicator
- Integrated fuse for line protection
- Can be fitted with solid-state relays or I/O modules

Commercial data

Item number	2972699
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61E3
GTIN	4017918088651
Weight per piece (including packing)	332.2 g
Weight per piece (excluding packing)	332.2 g
Customs tariff number	85369010
Country of origin	DE

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module



2972699

<https://www.phoenixcontact.com/us/products/2972699>

Technical data

Product properties

Product type	Multi-channel solid-state relay module
No. of channels	8
Compatible components	Digital I/O modules
With components	no

Input data

Input voltage range	4 V ... 32 V
Typical input current at U_N	30 mA (Optocoupler dependent)
Operating voltage display	Yellow LED
Status display/channel	Yellow LED

Output data

Compatible components	Digital I/O modules
Switching	
Limiting continuous current	4 A (Optocoupler dependent)
Error detection (line break / short-circuit)	no

Connection data

Input	
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	2
Number of positions	12
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Output	
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	16
Number of positions	3
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 10

Signaling

Status display present	yes
------------------------	-----

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module




2972699

<https://www.phoenixcontact.com/us/products/2972699>

Dimensions

Dimensional drawing



Width	180 mm
Height	77 mm
Depth	72 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
	DIN VDE 0160 (in relevant parts)

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module


2972699

<https://www.phoenixcontact.com/us/products/2972699>



Drawings

Dimensional drawing



A = without metal

B = with metal


UMK- 8 OM-R/MF/MKDS/P - Optocoupler module



2972699

<https://www.phoenixcontact.com/us/products/2972699>

Circuit diagram



Control logic: Plus switching

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module

2972699

<https://www.phoenixcontact.com/us/products/2972699>



Classifications

UNSPSC

UNSPSC 21.0

39122335

UMK- 8 OM-R/MF/MKDS/P - Optocoupler module

2972699

<https://www.phoenixcontact.com/us/products/2972699>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com