

2989556
<https://www.phoenixcontact.com/us/products/2989556>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Smart Managed Narrow Switch (SMN) with six 10/100 Mbps RJ45 ports and two 100 Mbps single mode SC format fiber optic ports

Product description

The Smart Managed Narrow switch (SMN) is an Ethernet switch suitable for industrial applications with six Fast Ethernet ports in RJ45 format and two single-mode Fast Ethernet FO ports in SC format

Commercial data

Item number	2989556
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNN122
GTIN	4046356478304
Weight per piece (including packing)	848.5 g
Weight per piece (excluding packing)	777 g
Country of origin	DE

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556

<https://www.phoenixcontact.com/us/products/2989556>

Technical data

Dimensions

Width	57 mm
Height	133 mm
Depth	125 mm

Material specifications

Color	gray aluminum
-------	---------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	6 (RJ45 ports)

Ethernet FO

Connection method	SC
Transmission speed	100 Mbps (full duplex)
Transmission physics	Single-mode fiberglass
Transmission length	36000 m (fiberglass with F-G 9/125 0.36 dB/km)
	32000 m (fiberglass with F-G 9/125 0.4 dB/km)
	26000 m (fiberglass with F-G 9/125 0.5 dB/km)
Wavelength	1300 nm
Signal LEDs	Data receive, link status
No. of channels	2 (SC single mode)

Serial (RS-232)

Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)
-------------------	---

Product properties

Product type	Switch
Product family	Managed Switch SMN
Type	Block design
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP),

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556

<https://www.phoenixcontact.com/us/products/2989556>

	PROFINET Device, Media Redundancy Protocol (MRP).
Switch functions	
Diagnostic functions	RMON History
	N:1-Portmirroring
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
Signal contact control voltage	24 V (typical)
Signal contact control current	100 mA
PROFINET conformance class	Conformance-Class B
PROFINET device function	PROFINET device
	Fast Startup
Filter functions	Quality of Service (4 priority classes)
	Port-Priorisierung
	VLAN
	IGMP Snooping (128 groups)
	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
	Static Multicast Filtering
Management	Web-based management (HTTP)
	SNMP v1/v2
	Serial interface (V.24)
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	FRD (Fast Ring Detection)
	Large Tree Support
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
Supported browsers	Internet Explorer 5.5 or higher
Additional functions	BootP
	DHCP-Client
Time synchronization	SNTP
Security functions	
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2

Electrical properties

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556

<https://www.phoenixcontact.com/us/products/2989556>

Maximum power dissipation for nominal condition	7.8 W
Transmission medium	Copper
	FO

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	18 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Typical current consumption	325 mA (at U _S = 24 V DC)

Function

Signal contact control voltage	24 V (typical)
Signal contact control current	100 mA

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (2000 m above mean sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-4:2007 + A1:2011
-----------------------	-----------------------------

System properties

Functionality

Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP),
-----------------	--

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556
<https://www.phoenixcontact.com/us/products/2989556>

	PROFINET Device, Media Redundancy Protocol (MRP).
--	---

System requirements

Supported browsers	Internet Explorer 5.5 or higher
--------------------	---------------------------------

Signaling

Status display	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
----------------	---

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556
<https://www.phoenixcontact.com/us/products/2989556>

Classifications

UNSPSC

UNSPSC 21.0	43222612
-------------	----------

FL SWITCH SMN 6TX/2FX SM - Industrial Ethernet Switch



2989556

<https://www.phoenixcontact.com/us/products/2989556>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com