

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, can be removed, Roll, white, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 10000, text field height: 6 mm, text field width: 15 mm

## Your advantages

- The EML-RM label is ideal for temporary marking
- This label features solid and reliable adhesion, but can also be easily removed again without any leftover residue. Once removed, it cannot be re-used
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-RM ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-RM ... markers in accordance with your requirements

## Commercial data

Item number	0830541
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356720533
Weight per piece (including packing)	333.5 g
Weight per piece (excluding packing)	333.5 g
Customs tariff number	39269097
Country of origin	DE

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



## Technical data

### Notes

General	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
---------	--

### Product properties

Product type	Gerätemarker
Product property	removable

### Marking

Number of individual labels	10000
Number of individual labels per row	1

### Dimensions

Width	15 mm
Length	6 mm

### Material specifications

Color	white (RAL 9010)
Material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
---------------	---------------------------------

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



Test duration	240 h
Rating 150 °C (180 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	> 15 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



Mounting type	adhesive
---------------	----------

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



## Classifications

### ECLASS

ECLASS-13.0	27281103
-------------	----------

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML-RM (15X6)RL-T - Label, can be removed

0830541

<https://www.phoenixcontact.com/us/products/0830541>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)