

# KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker carrier, transparent, unmarked, mounting type: Assembly with cable ties, cable diameter:  $\geq 9$  mm, text field height: 15 mm, text field width: 60 mm



## Product description

The cable marker carriers of type KMK UV are characterized by their extremely high UV and weather resistance. This has been established in accordance with DIN EN ISO 4892-2, test duration of 30,000 h - corresponds to 10 years in a central European climate.

They are therefore perfect for the permanent marking of cables outdoors.

The corresponding cable ties and marking labels can be found under the "Accessories" tab.

## Your advantages

- Plastic cable markers for insert labels, for assembly with cable binders
- Plastic cable markers for marking and bundling conductors and cables indoors
- The markers have eyelets and are attached with cable binders
- The marked insert label is protected from dirt by the sealing cap

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1014108       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BG12          |
| Product key                          | BG231A        |
| GTIN                                 | 4046356782685 |
| Weight per piece (including packing) | 4.41 g        |
| Weight per piece (excluding packing) | 4.34 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>



## Technical data

### Product properties

|                     |                 |
|---------------------|-----------------|
| Product type        | Marker carriers |
| Area of application | Outdoors        |

### Dimensions

|        |          |
|--------|----------|
| Width  | 64.02 mm |
| Height | 22.13 mm |
| Depth  | 8.68 mm  |

### Material specifications

|  |              |
|--|--------------|
| Color  | transparent  |
| Flammability rating according to UL 94               | HB           |
| Base element material                                | PA           |
| Components   | halogen-free |
| UV Exposure and Water Immersion according to UL 746C | f1           |

### Cable/line

|                         |           |
|-------------------------|-----------|
| External cable diameter | ≥ 9.00 mm |
|-------------------------|-----------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 30000 h                        |

#### Temperature resistance

|   |                                 |
|---|---------------------------------|
| Specification                                     | ANSI/UL 969-2018:03 (following) |
| Test duration                                     | 240 h                           |
| Rating 100 °C (121 °C)                            | Test passed                     |
| Specification                                     | ISO 175:2010 (following)        |
| Test duration                                     | 168 h                           |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                     |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed                     |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                     |
| IRM 901   | Test passed                     |
| IRM 902   | Test passed                     |

# KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>



## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## High pressure test

|               |                   |
|---------------|-------------------|
| Specification | IEC 60529:2001-02 |
| Result        | Test passed       |

## Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Ambient temperature (assembly)                      | 10 °C             |
| Resistance to UV radiation                          | yes               |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

# KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)