


# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 500 V, nominal current: 32 A, number of connections: 3, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: red

## Your advantages

- The consistent double function shaft offers every opportunity for time-saving potential distribution and accommodating test accessories
- User-friendly implementation of all potential branching tasks

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3044365       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1112        |
| GTIN                                 | 4046356751339 |
| Weight per piece (including packing) | 14.204 g      |
| Weight per piece (excluding packing) | 13.148 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Technical data

### Notes

#### General

|      |                                                                                              |
|------|----------------------------------------------------------------------------------------------|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. |
|------|----------------------------------------------------------------------------------------------|

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Multi-conductor terminal block |
| Product family        | UT                             |
| Area of application   | Machine building               |
|                       | Plant engineering              |
|                       | Process industry               |
| Number of connections | 3                              |
| Number of rows        | 1                              |
| Potentials            | 1                              |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                                                                     |                                              |
|-------------------------------------------------------------------------------------|----------------------------------------------|
| Number of connections per level                                                     | 3                                            |
| Nominal cross section                                                               | 4 mm <sup>2</sup>                            |
| Connection method                                                                   | Screw connection                             |
| Screw thread                                                                        | M3                                           |
| Tightening torque                                                                   | 0.6 ... 0.8 Nm                               |
| Stripping length                                                                    | 9 mm                                         |
| Internal cylindrical gage                                                           | A4                                           |
| Connection in acc. with standard                                                    | IEC 60947-7-1                                |
| Conductor cross-section rigid                                                       | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Cross section AWG                                                                   | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible                                                    | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]                                             | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                   | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Flexible conductor cross-section (ferrule with plastic sleeve)                      | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| 2 conductors with same cross section, solid                                         | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible                                      | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

|                                                                                           |                                                                                                                                                                   |
|-------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>                                                                                                                         |
| Nominal current                                                                           | 32 A                                                                                                                                                              |
| Maximum load current                                                                      | 41 A (In the case of a 6 mm <sup>2</sup> conductor cross section, the maximum load current must not be exceeded by the total current of all connected conductors) |
| Nominal voltage                                                                           | 500 V                                                                                                                                                             |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                                                                                                                                 |

## Ex data

### Rated data (ATEX/IECEx)

|                                                                          |                                     |
|--------------------------------------------------------------------------|-------------------------------------|
| Identification                                                           | Ⓔ II 2 GD Ex eb IIC Gb              |
| Operating temperature range                                              | -60 °C ... 110 °C                   |
| Ex-certified accessories                                                 | 3047141 D-UT 2,5/4-TWIN             |
|                                                                          | 3047109 DS-UT 2,5/4                 |
|                                                                          | 3047183 ATP-UT-TWIN                 |
|                                                                          | 1212587 SF-SL 0,6X3,5-100 S-VDE     |
|                                                                          | 3022276 CLIPFIX 35-5                |
|                                                                          | 3022218 CLIPFIX 35                  |
| List of bridges                                                          | Plug-in bridge / FBS 2-6 / 3030336  |
|                                                                          | Plug-in bridge / FBS 3-6 / 3030242  |
|                                                                          | Plug-in bridge / FBS 4-6 / 3030255  |
|                                                                          | Plug-in bridge / FBS 5-6 / 3030349  |
|                                                                          | Plug-in bridge / FBS 10-6 / 3030271 |
|                                                                          | Plug-in bridge / FBS 20-6 / 3030365 |
| Bridge data                                                              | 27 A (4 mm <sup>2</sup> )           |
| Ex temperature increase                                                  | 40 K (32.5 A / 4 mm <sup>2</sup> )  |
| for bridging with bridge                                                 | 352 V                               |
| - At bridging between non-adjacent terminal blocks                       | 352 V                               |
| - At bridging between non-adjacent terminal blocks via PE terminal block | 275 V                               |
| - At cut-to-length bridging with cover                                   | 220 V                               |
| - At cut-to-length bridging with partition plate                         | 275 V                               |
| Rated insulation voltage                                                 | 320 V                               |
| output                                                                   | (Permanent)                         |

### Ex level General

|                      |         |
|----------------------|---------|
| Rated voltage        | 352 V   |
| Rated current        | 29 A    |
| Maximum load current | 35 A    |
| Contact resistance   | 0.44 mΩ |

### Ex connection data General

|                         |                   |
|-------------------------|-------------------|
| Torque range            | 0.6 Nm ... 0.8 Nm |
| Nominal cross section   | 4 mm <sup>2</sup> |
| Rated cross section AWG | 12                |

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

|                                                       |                                              |
|-------------------------------------------------------|----------------------------------------------|
| Connection capacity rigid                             | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Connection capacity AWG                               | 26 ... 10                                    |
| Connection capacity flexible                          | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Connection capacity AWG                               | 26 ... 12                                    |
| 2 conductors with same cross section, solid           | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with the same cross-section AWG rigid    | 26 ... 16                                    |
| 2 conductors with same cross section, stranded        | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with the same cross-section AWG flexible | 26 ... 16                                    |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 57.8 mm |
| Depth on NS 35/7,5 | 47.5 mm |
| Depth on NS 35/15  | 55 mm   |

## Material specifications

|                                                                  |                |
|------------------------------------------------------------------|----------------|
| Color                                                            | red (RAL 3001) |
| Flammability rating according to UL 94                           | V0             |
| Insulating material group                                        | I              |
| Insulating material                                              | PA             |
| Static insulating material application in cold                   | -60 °C         |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C         |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

### Temperature-rise test

|                                                |                                |
|------------------------------------------------|--------------------------------|
| Requirement temperature-rise test              | Increase in temperature ≤ 45 K |
| Result                                         | Test passed                    |
|                                                | Test passed                    |
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA                        |
| Short-time withstand current 6 mm <sup>2</sup> | 0.72 kA                        |
| Result                                         | Test passed                    |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 1 N         |
| Result                  | Test passed |

### Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross-section/weight | 0.14 mm <sup>2</sup> / 0.2 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg    |
|                                | 6 mm <sup>2</sup> / 1.4 kg    |
| Result                         | Test passed                   |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                |
|------------------------|------------------------------------------------|
| Specification          | EN 50155:2021                                  |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g                                          |
| Test duration per axis | 5 h                                            |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 30g                                 |
| Shock duration                 | 18 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|                                 |                                                                                                                              |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------|

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C ( )                                                       |
| Permissible humidity (operation)         | 20 % ... 90 %                                                             |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Drawings

Circuit diagram



# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3044365>

### DNV

Approval ID: TAE00001S9



### CSA

Approval ID: 13631



### IECEE CB Scheme

Approval ID: DE1-62912

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | 500 V                 | -                     | -                 | -                           |



### cULus Recognized

Approval ID: E60425

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B | 300 V                 | 30 A                  | 26 - 10           | -                           |
| C | 300 V                 | 30 A                  | 26 - 10           | -                           |



### VDE approval of drawings

Approval ID: 40040772

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | 500 V                 | 32 A                  | -                 | 0.14 - 6                    |



### CSA

Approval ID: 13631



### ATEX

Approval ID: KEMA06ATEX0017U



### cUL Recognized

Approval ID: E192998

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

|   |       |      |         |   |
|---|-------|------|---------|---|
|   | 150 V | 30 A | 26 - 10 | - |
| C |       |      |         |   |
|   | 150 V | 30 A | 26 - 10 | - |



**EAC Ex**

Approval ID: KZ 7500525010101950



**IECEx**

Approval ID: IECEx KEM 06.0013U



**UL Recognized**

Approval ID: E192998

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |
|   | 150 V                 | 30 A                  | 26 - 10           | -                           |
| C |                       |                       |                   |                             |
|   | 150 V                 | 30 A                  | 26 - 10           | -                           |



**CCC**

Approval ID: 2020322313000622



**UKCA-EX**

Approval ID: DEKRA 21UKEX0305U

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UT 4-TWIN RD - Feed-through terminal block



3044365

<https://www.phoenixcontact.com/us/products/3044365>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 1da22ec6-4d3b-4d83-a200-6fe5ed881c6d |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)