

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 34 mm ... 44 mm, shielding: no, connecting thread: M63 x 1.5, color: lightgray RAL 7035

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1417658       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF68          |
| Product key                          | AF7DCX        |
| GTIN                                 | 4055626121611 |
| Weight per piece (including packing) | 106.6 g       |
| Weight per piece (excluding packing) | 106.6 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | TR            |

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

## Technical data

### Mounting

|               |                                                                                                                                         |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | 1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------|


### Product properties

|                                |                   |
|--------------------------------|-------------------|
| Product type                   | Cable screw gland |
| Application                    | Standard          |
| No. of conductors              | 1                 |
| Manufacturer                   | BIMED             |
| Manufacturer Designation       | BM-20             |
| Shielded                       | no                |
| Execution of the strain relief | A                 |

### Characteristics

|                          |   |
|--------------------------|---|
| Category of shock impact | 4 |
| Design, Strain relief    | A |

### Dimensions

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Length                          | 75 mm                                                                                |
| Length of the connecting thread | 18 mm                                                                                |
| Hole diameter                   | 63.1 mm ... 63.3 mm                                                                  |
| Wrench size, union nut          | 65 mm                                                                                |
| Wrench size, support            | 65 mm                                                                                |
| Hexagon angular dimension       | 72.2 mm                                                                              |
| Thread type connection side     | M63 x 1.5                                                                            |
| Thread pitch                    | 1.5 mm                                                                               |

### Connection data

|                   |                              |
|-------------------|------------------------------|
| Tightening torque | 20 Nm $\pm$ 2.5 Nm (Cap nut) |
|                   | 12 Nm (Support sleeve)       |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color                                  | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V2                    |
| Seal material Cable seal               | CR                    |
| Material for screw connection          | PA                    |

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

## Cable/line

|                                 |                                |
|---------------------------------|--------------------------------|
| External cable diameter Cable 1 | 34 mm ... 44 mm (for UL 514 B) |
|---------------------------------|--------------------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                            |
|---------------------------------|----------------------------|
| Degree of protection            | IP66                       |
|                                 | IP68 (5 bar / 0.5 h)       |
| Enclosure rating (NEMA)         | 1                          |
|                                 | 4                          |
|                                 | 4X                         |
|                                 | 12                         |
|                                 | 13                         |
| Ambient temperature (operation) | -40 °C ... 100 °C (static) |

# G-INS-M63-L68L-PNES-LG - Cable gland


1417658

<https://www.phoenixcontact.com/us/products/1417658>



## Drawings

Dimensional drawing



Dimensional drawing

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417658>

### DNV

Approval ID: TAE00003WX



### UL Listed

Approval ID: E199260



### cUL Listed

Approval ID: E199260

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140801 |
| ECLASS-15.0 | 27140801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000441 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

# G-INS-M63-L68L-PNES-LG - Cable gland



1417658

<https://www.phoenixcontact.com/us/products/1417658>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 0.808 kg CO2e                            |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)