

US-EMLP (35X9) SR CUS - Plastic label



0830108

<https://www.phoenixcontact.com/us/products/0830108>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, can be ordered: by card, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 45, text field height: 9 mm, text field width: 35 mm



Your advantages

- All US-EMLP ... device markers can also be supplied labeled according to customer requirements
- PVC material flammability rating V0 in accordance with UL 94

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0830108 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8149 |
| GTIN | 4046356614702 |
| Weight per piece (including packing) | 20.6 g |
| Weight per piece (excluding packing) | 17.79 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | Gerätemarker |
|--------------|--------------|

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 45 |
| Number of individual labels per row | 3 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|----------|
| Width | 34.65 mm |
| Height | 9.00 mm |
| Depth | 0.55 mm |
| Length | 9 mm |

Material specifications

| | |
|-------------------|---------------|
| RoHS compliant | yes |
| Foil strength | 500 µm |
| Adhesive strength | 50 µm |
| Adhesive | Acrylic |
| Color | silver |
| Material | PVC |
| Components | Silicone-free |

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |
| Shelf life | 12 months |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

US-EMLP (35X9) SR CUS - Plastic label



0830108

<https://www.phoenixcontact.com/us/products/0830108>

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

US-EMLP (35X9) SR CUS - Plastic label



0830108

<https://www.phoenixcontact.com/us/products/0830108>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

US-EMLP (35X9) SR CUS - Plastic label



0830108

<https://www.phoenixcontact.com/us/products/0830108>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com