

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, For TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, frontal insertion, compression: Trapezoidal crimp, weight 302 g, black

## Your advantages

- Large cross section range from 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>
- For ferrules up to a length of 18 mm
- Comfortable to use, thanks to low grip span with optimum manual force progression
- Process reliability, thanks to pressure lock and self-adjusting die
- Suitable for TWIN ferrules, thanks to continuous automatic adjustment

## Commercial data

Item number	1134913
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4063151067168
Weight per piece (including packing)	389.4 g
Weight per piece (excluding packing)	301.8 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Technical data

### Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp
Product property	Rotating, self-adjusting crimping die (duo versions) Compact, lightweight, and optimally balanced
	Low grip span
	Ergonomic two-component handle
	Low actuation force
	Suitable for TWIN ferrules
	Handle with non-slip pad
	Tool-free unlockable pressure lock

### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>
AWG min	26
AWG max	8

### Electrical properties

Fuse	DIN 46228-1, DIN 46228-4
------	--------------------------

### Connection data

#### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 10 mm <sup>2</sup> (2 x 0.5 mm <sup>2</sup> ... 2 x 4 mm <sup>2</sup> )
Cross section range AWG	26 ... 8 (2 x AWG 20 ... 2 x AWG 12)

### Dimensions

Width	65 mm
Height	25 mm
Length	180 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1134913>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 9.0	EC000168
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)