

SPE-T1-CIM-SF - Connector

1343953

<https://www.phoenixcontact.com/us/products/1343953>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, design: IEC 63171-2, degree of protection: IP20, number of positions: 2, 1 Gbps, material: Metal, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, Single Pair Ethernet

Your advantages

- Data transmission up to 600 MHz
- Compact design
- Connectors in accordance with IEC 63171-2
- Mechanical interlock with locking clip
- High shock and vibration resistance
- 360° shielding
- Robust industrial design
- Assembly without special tools

Commercial data

Item number	1343953
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB13
Product key	ABNBAB
GTIN	4063151655280
Weight per piece (including packing)	9.16 g
Weight per piece (excluding packing)	9.16 g
Customs tariff number	85366990
Country of origin	DE

SPE-T1-CIM-SF - Connector

1343953

<https://www.phoenixcontact.com/us/products/1343953>



Technical data

Product properties

Product type	Data connector (cable side)
Type	SPE
Sensor type	Single Pair Ethernet
Number of positions	2
Connection profile	SPE
Number of slots	2
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	2250 V DC
Rated current	2 A
Frequency range	600 MHz
Insulation resistance	> 500 MΩ
Contact resistance	< 20 mΩ
Transmission medium	Copper
Transmission speed	1 Gbps (in accordance with IEEE 802.3 bp) 100 Mbps (in accordance with IEEE 802.3 bw) 10 Mbps (in accordance with IEEE 802.3 cg)
Transmission characteristics (category)	CAT B (IEC 63171)
Transmission speed	1 Gbps
Power transmission	PoDL

Connection data

Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
Conductor cross section	0.18 mm² ... 0.45 mm²

Interfaces

Transmission speed	100 Mbps (in accordance with IEEE 802.3 bw) 1 Gbps (in accordance with IEEE 802.3 bp) 10 Mbps (in accordance with IEEE 802.3 cg)
--------------------	--

Dimensions

SPE-T1-CIM-SF - Connector

1343953

<https://www.phoenixcontact.com/us/products/1343953>



Width	7.5 mm
Height	11.3 mm
Length	32.85 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PC

Cable/line

External cable diameter	3.6 mm ... 5.7 mm
Stripping length of the individual wire	15 mm
Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250.00 V DC
Halogen-free	yes

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 750

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-25 °C ... 85 °C

Mounting

Mounting type	For field assembly
Assembly note	Max. 4x reconnectable with the same or larger conductor cross-section

SPE-T1-CIM-SF - Connector

1343953

<https://www.phoenixcontact.com/us/products/1343953>



Classifications

ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SPE-T1-CIM-SF - Connector

1343953

<https://www.phoenixcontact.com/us/products/1343953>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a)
SCIP	02b17642-abbd-467b-b196-13cc0019557b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com