

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS PA (31.25 kbps), 3-position, PVC, blue RAL 5015, shielded, Plug angled M12, coding: A, on free cable end, cable length: 10 m, For Ex area with high-grade steel knurl

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1419099       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF04          |
| Product key                          | AF1CCG        |
| GTIN                                 | 4046356541664 |
| Weight per piece (including packing) | 683 g         |
| Weight per piece (excluding packing) | 683 g         |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

## Technical data

### Notes

|         |                                                                                                                   |
|---------|-------------------------------------------------------------------------------------------------------------------|
| General | For applications in circuits of intrinsic safety protection type "i".<br>Electrical values following EN 60079-14. |
|---------|-------------------------------------------------------------------------------------------------------------------|

### Product properties

|                      |                         |
|----------------------|-------------------------|
| Product type         | Data cable preassembled |
| Application          | Process technology      |
| Sensor type          | PROFIBUS PA             |
| Number of positions  | 3                       |
| No. of cable outlets | 1                       |
| Shielded             | yes                     |
| Coding               | A                       |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Interfaces

|                      |                         |
|----------------------|-------------------------|
| Bus system           | PROFIBUS PA             |
| Signal type/category | PROFIBUS PA, 31.25 kbps |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|                       |            |
|-----------------------|------------|
| Nominal voltage $U_N$ | 48 V AC    |
|                       | 60 V DC    |
| Nominal current $I_N$ | 4 A        |
| Transmission medium   | Copper     |
| Transmission speed    | 31.25 kbps |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Material specifications

|                                        |     |
|----------------------------------------|-----|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR |

### Connection data

|                       |
|-----------------------|
| Connection assignment |
|-----------------------|

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

|                                                           |                        |
|-----------------------------------------------------------|------------------------|
| Contact   Color (signal designation)   Contact (optional) | 1 (Plug)   OG (DATA+)  |
|                                                           | 3 (Plug)   BU (DATA-)  |
|                                                           | 4 (Plug)   SR (shield) |

## Connector

### Connection 1

|                                 |                                                         |
|---------------------------------|---------------------------------------------------------|
| Type                            | Plug angled M12                                         |
| Number of positions             | 3                                                       |
| Coding type                     | A (Standard)                                            |
| Material                        | CuSn (Contact)                                          |
|                                 | Ni/Au (Contact surface)                                 |
|                                 | TPU GF (Contact carrier)                                |
|                                 | TPU, hardly inflammable, self-extinguishing (Grip body) |
| Ambient temperature (operation) | Stainless steel (Screw connection)                      |
|                                 | -25 °C ... 90 °C                                        |


### Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

### Fieldbus FOUNDATION/PROFIBUS PA, blue [961]

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Cable weight                    | 56.552 kg/km                                                                         |
| Number of positions             | 2                                                                                    |
| Shielded                        | yes                                                                                  |
| Cable type                      | Fieldbus FOUNDATION/PROFIBUS PA, blue [961]                                          |
| Conductor structure             | 2xAWG18/7 + 1xAWG20/7                                                                |
| Signal speed                    | 0.66 c                                                                               |
| Conductor structure signal line | 7x 0.40 mm                                                                           |
| AWG signal line                 | 18                                                                                   |
| Conductor cross section         | 2x 0.75 mm <sup>2</sup> (Signal line)                                                |
|                                 | 1x 0.5 mm <sup>2</sup> (Drain wire)                                                  |
| Wire diameter incl. insulation  | 2.24 mm ±0.05 mm                                                                     |
| External cable diameter         | 7.50 mm ±0.25 mm                                                                     |
| Outer sheath, material          | PVC                                                                                  |

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

|                                             |                                                   |
|---------------------------------------------|---------------------------------------------------|
| External sheath, color                      | blue RAL 5015                                     |
| Conductor material                          | Tin-plated Cu litz wires                          |
| Material wire insulation                    | PO (Signal line)                                  |
| Single wire, color                          | blue, orange                                      |
| Thickness, insulation                       | 0.50 mm                                           |
| Thickness, outer sheath                     | 1.00 mm                                           |
| Twisted pairs                               | 2 cores to the pair                               |
| Overall twist                               | One pair with one drain wire and fillers for core |
| Optical shield covering                     | 100 %                                             |
| Max. conductor resistance                   | ≤ 19.35 Ω/km (Signal line)                        |
|                                             | 26 Ω/km (shield)                                  |
| Cable capacity                              | 147 pF/m (at 1 kHz, core/shield)                  |
|                                             | ≤ 3.94 pF/m (capacitance unbalance)               |
| Working capacitance                         | 78 nF (at 1 kHz)                                  |
| Cable impedance                             | 100 Ω ±20 % (At 31.25 kHz)                        |
| Nominal voltage, cable                      | 300 V                                             |
| Smallest bending radius, fixed installation | 75 mm                                             |
| Tensile strength                            | 260 N                                             |
| Shield attenuation                          | 3.00 dB/km (at 39 kHz)                            |
| Flame resistance                            | UL 1685 (CSA FT 4)                                |
|                                             | UL 1685 (vertical tray)                           |
|                                             | UL 1666 (riser)                                   |
| Special properties                          | UL standards PLTC-ER and ITC                      |
| Ambient temperature (operation)             | -40 °C ... 105 °C (cable, fixed installation)     |

## Environmental and real-life conditions

### Ambient conditions

|                      |       |
|----------------------|-------|
| Degree of protection | IP65  |
|                      | IP67  |
|                      | IP68  |
|                      | IP69K |

## Drawings

Dimensional drawing



M12 x 1 male plug, angled

1419099


<https://www.phoenixcontact.com/us/products/1419099>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Circuit diagram



Contact assignment of the M12 plug

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-3P-M12MR/10,0-961 VA - Bus system cable



1419099

<https://www.phoenixcontact.com/us/products/1419099>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)