

NBC-MSBP-5P-M16/1,0-920/FR SCO - Network cable



1419545

<https://www.phoenixcontact.com/us/products/1419545>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, degree of protection: IP65/IP67, cable length: 1 m, number of positions: 5, CANopen®

Commercial data

Item number	1419545
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	ABQSAE
GTIN	4055626181356
Weight per piece (including packing)	99.4 g
Weight per piece (excluding packing)	99.4 g
Country of origin	DE

1419545

<https://www.phoenixcontact.com/us/products/1419545>

Technical data

Product properties

Sensor type	CANopen®
Number of positions	5
Shielded	yes

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Transmission medium	Copper
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Material specifications

Flammability rating according to UL 94	V2
--	----

Connector

Connection 1

Type	Flush-type female connector straight M12
------	--

Connection 2

Type	Plug straight RJ45
------	--------------------

Cable/line

Cable length	1.00 m
Cable type	Ethernet

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67



1419545

<https://www.phoenixcontact.com/us/products/1419545>

Classifications

UNSPSC

UNSPSC 21.0	26121604
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%