

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Maritime-Panel PC, 17.8 cm / 7"-TFT display (Analog resistive (GFG)), 800 x 480 pixel(s) (WVGA), 262144 colors, Intel® Atom™ E680T 1.6 GHz, 4x USB Host 2.0, 1x COM (RS-232), 1x COM (RS-232/485), 2x Ethernet (10/100/1000 Mbps), RJ45, Windows® Embedded Standard 7, TSvisIT, DualCAN.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2401287 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | DRCBCE |
| GTIN | 4055626107639 |
| Weight per piece (including packing) | 900 g |
| Weight per piece (excluding packing) | 900 g |
| Country of origin | DE |

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|--------------|----------|
| Product type | Panel PC |
| Application | Maritime |

Computer data

| | |
|---------------------|------------------------------|
| Processor | Intel® Atom™ E680T 1.6 GHz |
| Operating system | Windows® Embedded Standard 7 |
| RAM | 2 GB DDR2 SDRAM |
| Data storage system | SATA DOM SSD (SLC), 8 GB |
| Slots | 1x SD |
| Extras | Maritime with keys |

Display

| | |
|-----------------------|---------------------------------|
| Display type | 17.8 cm / 7"-TFT |
| Screen resolution | 800 x 480 Pixel(s) (WVGA) |
| Touch technology | Analog resistive (GFG) |
| Display lighting type | LED |
| Brightness | 350 cd/m², typical (adjustable) |
| MTBF | 40000 h |
| Color spectrum | 262144 colors |
| Reading angle left | 70.00 ° |
| Reading angle right | 70.00 ° |
| Reading angle top | 65.00 ° |
| Reading angle bottom | 65.00 ° |

System properties

| | |
|---------------|---------|
| User software | TSvisIT |
|---------------|---------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

Supply

| | |
|-----------------------------|-------|
| Typical current consumption | 0.7 A |
|-----------------------------|-------|

Real-time clock

| | |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

Supply

| | |
|-------------------|---------------|
| Power supply unit | 24 V DC ±20 % |
|-------------------|---------------|

Interfaces

| | |
|------------|---|
| Interfaces | 4x USB Host 2.0 1x COM (RS-232) 1x COM (RS-232/485) |
| Network | 2x Ethernet (10/100/1000 Mbps), RJ45 |
| Bus system | DualCAN |

Dimensions

External dimensions

| | |
|------------------------|--|
| Width / Height / Depth | 234 mm / 189 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

Installation dimensions

| | |
|-------------------------------------|-------------------------|
| Width / Height / Installation depth | 200 mm / 155 mm / 95 mm |
|-------------------------------------|-------------------------|

Material specifications

| | |
|----------------------|---------------------------|
| Material front plate | Aluminum (black anodized) |
| Housing material | Steel sheet, zinc-plated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---------------------------------------|
| Degree of protection | IP65 (front), IP20 (back) NEMA 4X |
| Ambient temperature (operation) | 0 °C ... 55 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |
| Altitude | 3000 m |
| Permissible humidity (operation) | 20 % ... 85 % |
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 0.7g, in accordance with EN 60068-2-6 |

Mounting

| | |
|---------------|-------------|
| Mounting type | Bolt fixing |
|---------------|-------------|

Environmental product compliance

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-15 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com