

PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection plug for the base element, common mode voltage coarse and fine protection for four lines with a common reference potential. Design: 48 V DC

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

Item number	2858014
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL21
Product key	CL2111
GTIN	4017918828325
Weight per piece (including packing)	26.27 g
Weight per piece (excluding packing)	21.768 g
Customs tariff number	85363010
Country of origin	DE

PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Technical data

Product properties

Product type	Surge protection for MCR technology
Product family	PLUGTRAB PT
IEC test classification	C1 C2 C3 D1
VDE requirement class	C1 C2 C3 D1
Type	Male
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00

Insulation characteristics

Ovvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	48 V DC
-----------------------	---------

Connection data

Connection method	Screw connection (in connection with the base element)
Screw thread	M3
Tightening torque	0.8 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	45 mm
Depth	52 mm
Horizontal pitch	1 Div.
Complete module width	17.7 mm
Complete module height	90 mm

PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Complete module depth	65.5 mm
-----------------------	---------

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data	
Open side panel	No

Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
Maximum continuous operating voltage U_C	53 V DC 37 V AC
Rated current	300 mA (45 °C)
Operating effective current I_C at U_C	≤ 5 µA
Protective conductor current I_{PE}	≤ 1 µA (with PT 4X1+F-BE) ≤ 20 µA (Directly grounded)
Nominal discharge current I_n (8/20) µs (line-ground)	10 kA
Pulse discharge current I_{imp} (10/350) µs	2.5 kA (per path)
Total discharge current I_{Total} (8/20) µs	20 kA
Max. discharge current I_{max} (8/20) µs maximum (line-earth)	10 kA
Nominal pulse current I_{an} (10/1000) µs (line-earth)	17 A
Output voltage limitation at 1 kV/µs (line-earth) spike	≤ 75 V
Output voltage limitation at 1 kV/µs (line-earth) static	≤ 70 V
Residual voltage at I_n (conductor-ground)	≤ 70 V
Voltage protection level U_p (line-earth)	≤ 130 V (C2 - 10 kV / 5 kA)
Response time t_A (line-earth)	≤ 1 ns
Input attenuation a_E , asym.	0.5 dB (≤ 1.7 MHz)
Cut-off frequency f_g (3 dB), asym. (PE) in 50 Ω system	typ. 9 MHz
Capacity (Core-Earth)	0.9 nF
Resistance per path	4.7 Ω
Surge protection fault message	none
Max. required back-up fuse	315 mA (T)
Impulse durability (line-earth)	C2 - 10 kV / 5 kA D1 - 2.5 kA

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Standards and regulations

VDE requirement class	C1 C2 C3 D1
Standards/specifications	IEC 61643-21
Note	2000

Mounting

Mounting type	on base element
---------------	-----------------

PT 4X1-48DC-ST - Surge protection plug


2858014

<https://www.phoenixcontact.com/us/products/2858014>




Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Classifications

ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

ETIM

ETIM 9.0	EC000943
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

PT 4X1-48DC-ST - Surge protection plug

2858014

<https://www.phoenixcontact.com/us/products/2858014>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f4c8ad0c-aabf-42a4-a71f-282f81be493a

EF3.0 Climate Change

CO2e kg	1.179 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com