

# PACT MCR-V2-10020-129-1600-1A1 - Current transformer



2905888

<https://www.phoenixcontact.com/us/products/2905888>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 1600 A AC primary current; 1 A AC secondary current; accuracy class 1; 10 VA rated power

## Commercial data

Item number	2905888
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMMA11
GTIN	4055626004891
Weight per piece (including packing)	538.4 g
Weight per piece (excluding packing)	250 g
Country of origin	DE

# PACT MCR-V2-10020-129-1600-1A1 - Current transformer



2905888

<https://www.phoenixcontact.com/us/products/2905888>

## Technical data

### Product properties

Product type	Current transformer
--------------	---------------------

### Electrical properties

Rated insulation voltage	1 kV (Phase/neutral conductor)
--------------------------	--------------------------------

#### General

Can be calibrated	no
Converter type	Window-type current transformer

### Input data

#### Current transformer

Rated power	10 VA
Thermal rated short-time current	$I_{th} = 60 * I_n$
Thermal rated continuous current	$I_d = 1.2 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency $f_n$	50 Hz
	60 Hz
Primary rated current $I_{pn}$	0 A ... 1600 A
Can be calibrated	no
Converter type	Window-type current transformer

### Output data

#### Signal

Secondary rated current $I_{sn}$	1 A AC
Surge current limitation factor	FS 5
Accuracy class	1

### Connection data

Connection method	Screw connection
Conductor cross-section flexible	2x 2.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Secondary terminals)

### Dimensions

#### Item dimensions

Width	30 mm
Height	156 mm
Depth	129 mm

#### Item dimensions with alternative mounting

Width	129 mm
Height	156 mm

# PACT MCR-V2-10020-129-1600-1A1 - Current transformer



2905888

<https://www.phoenixcontact.com/us/products/2905888>

Depth	30 mm
-------	-------

Copper rail	
-------------	--

Width	100 mm
Height	10 mm

Copper rail 2	
---------------	--

Width	80 mm
Height	64 mm

Circular conductor	
--------------------	--

Diameter	85 mm
----------	-------

## Material specifications

Housing material	PA 6.6
------------------	--------

## Environmental and real-life conditions

Ambient conditions	
--------------------	--

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C
Permissible humidity (operation)	Use only indoors, non-condensing
Insulating material class	E

## Approvals

CE	
----	--

Certificate	CE-compliant
-------------	--------------

UKCA	
------	--

Certificate	UKCA-compliant
-------------	----------------

## Standards and regulations

Standards/regulations	EN 50178
	EN 61869

# PACT MCR-V2-10020-129-1600-1A1 - Current transformer



2905888

<https://www.phoenixcontact.com/us/products/2905888>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)