

# UP 4/ 1-L - Plug

3060021

<https://www.phoenixcontact.com/us/products/3060021>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of positions: 1, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup>- 6 mm<sup>2</sup>, color: gray

## Product description

Connector element left, left housing without engagement pin, right opened without cover

## Your advantages

- The COMBI plugs for self-assembly provide solutions that users can implement themselves
- The screw plugs can be combined with COMBI terminal blocks with all forms of connection technology and are available in two versions
- The plugs are assembled directly on site by snapping together 1-position plug elements
- The plug design enables space-saving potential distribution by using four-conductor terminal blocks with two slots

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3060021       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1144        |
| GTIN                                 | 4046356088343 |
| Weight per piece (including packing) | 4.9 g         |
| Weight per piece (excluding packing) | 4.863 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | TR            |

# UP 4/ 1-L - Plug

3060021

<https://www.phoenixcontact.com/us/products/3060021>



## Technical data

### Notes

|                    |                                                                                                                                                                         |
|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Terminal plug |
| Number of positions | 1             |
| Pitch               | 6.2 mm        |
| Potentials          | 1             |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                     |      |
|---------------------|------|
| Rated surge voltage | 8 kV |
|---------------------|------|

### Connection data

|                                                                                           |                                                       |
|-------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                     |
| Connection method                                                                         | Screw connection                                      |
| Screw thread                                                                              | M3                                                    |
| Tightening torque                                                                         | 0.6 ... 0.8 Nm                                        |
| Stripping length                                                                          | 9 mm                                                  |
| Internal cylindrical gage                                                                 | A4                                                    |
| Connection in acc. with standard                                                          | IEC 61984                                             |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>             |
| Cross section AWG                                                                         | 24 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>             |
| Conductor cross-section, flexible [AWG]                                                   | 24 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| 2 conductors with same cross section, solid                                               | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>           |
| 2 conductors with same cross section, flexible                                            | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>           |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>           |
| Nominal current                                                                           | 32 A                                                  |
| Maximum load current                                                                      | 32 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage                                                                           | 800 V                                                 |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                     |

# UP 4/ 1-L - Plug

3060021

<https://www.phoenixcontact.com/us/products/3060021>



## Dimensions

|        |         |
|--------|---------|
| Width  | 6.2 mm  |
| Height | 21 mm   |
| Depth  | 41.2 mm |
| Length | 21 mm   |
| Pitch  | 6.2 mm  |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg      |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (operation)         | 20 % ... 90 %                                                             |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

# UP 4/ 1-L - Plug


3060021

<https://www.phoenixcontact.com/us/products/3060021>

## Drawings

Schematic diagram





Circuit diagram



# UP 4/ 1-L - Plug

3060021

<https://www.phoenixcontact.com/us/products/3060021>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3060021>



**CSA**

Approval ID: 13631



**IECEE CB Scheme**

Approval ID: NL-34722\_A1

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 800 V                 | 32 A                  | -                 | -                           |



**cULus Recognized**

Approval ID: E60425

|                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|----------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| B                          |                       |                       |                   |                             |
|                            | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Multi-conductor connection | 600 V                 | 30 A                  | 26 - 14           | -                           |
| C                          |                       |                       |                   |                             |
|                            | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Multi-conductor connection | 600 V                 | 30 A                  | 26 - 14           | -                           |



**KEMA-KEUR**

Approval ID: 71-114072 REV.1

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 800 V                 | 32 A                  | -                 | -                           |



**CSA**

Approval ID: 13631



**EAC**

Approval ID: KZ7500651131219505

# UP 4/ 1-L - Plug

3060021

<https://www.phoenixcontact.com/us/products/3060021>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002021 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UP 4/ 1-L - Plug



3060021  
<https://www.phoenixcontact.com/us/products/3060021>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)