


PTT 1,5/S-2L BU - Feed-through terminal block



3210357

<https://www.phoenixcontact.com/us/products/3210357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 400 V, nominal current: 9 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 1.5 mm², 1st and 2nd level, cross section: 0.14 mm² - 1.5 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3210357 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE2232 |
| GTIN | 4046356942041 |
| Weight per piece (including packing) | 9.632 g |
| Weight per piece (excluding packing) | 9.632 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



Technical data

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | Feed-through terminal block |
| Product family | PT |
| Number of connections | 4 |
| Number of rows | 2 |
| Potentials | 2 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 0.56 W |

Connection data

| | |
|---------------------------------|---------------------|
| Number of connections per level | 2 |
| Nominal cross section | 1.5 mm ² |

1st and 2nd level

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 8 mm ... 10 mm |
| Internal cylindrical gage | A1 / B1 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.14 mm ² ... 1.5 mm ² |
| Cross section AWG | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 1 mm ² (Using the AI-S 1-8 TQ ferrule, Item No. 1200293, is recommended) |
| Nominal current | 9 A |
| Maximum load current | 9 A |
| Nominal voltage | 400 V |
| Nominal cross section | 1.5 mm ² |

1st and 2nd level Connection cross sections directly pluggable

| | |
|---|--|
| Conductor cross-section rigid | 0.25 mm ² ... 1.5 mm ² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.34 mm ² ... 1 mm ² |

Dimensions

| | |
|-------|--------|
| Width | 3.5 mm |
|-------|--------|

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



| | |
|--------------------|---------|
| End cover width | 0.8 mm |
| Height | 86 mm |
| Depth | 41.1 mm |
| Depth on NS 35/7,5 | 42.6 mm |
| Depth on NS 35/15 | 50.1 mm |

Material specifications

| | |
|---|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 27,5 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

| | |
|-----------------|-----|
| Mechanical data | |
| Open side panel | Yes |

Environmental and real-life conditions

| | |
|--|--|
| Ambient conditions | |
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|---------------|-----------|

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



NS 35/15

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



Drawings

Circuit diagram



PTT 1,5/S-2L BU - Feed-through terminal block



3210357

<https://www.phoenixcontact.com/us/products/3210357>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3210357>

| | | CSA | | |
|---|--|-----------------------|-----------------------|-------------------|
| | | Approval ID: 2030668 | | |
| | | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| B | | 300 V | 10 A | 26 - 16 |
| C | | 300 V | 10 A | 26 - 16 |

| | | EAC | | |
|--|--|-----------------------------------|--|--|
| | | Approval ID: RU C-DE.BL08.B.00644 | | |

| | | cULus Recognized | | |
|---|-------------|-----------------------|-----------------------|-------------------|
| | | Approval ID: E60425 | | |
| | | Nominal voltage U_N | Nominal current I_N | Cross section AWG |
| B | | 300 V | 10 A | 26 - 16 |
| | upper level | 300 V | 10 A | 26 - 16 |
| | lower level | 300 V | 10 A | 26 - 16 |
| C | | 300 V | 10 A | 26 - 16 |
| | upper level | 300 V | 10 A | 26 - 16 |
| | lower level | 300 V | 10 A | 26 - 16 |

| | | DNV | | |
|--|--|-------------------------|--|--|
| | | Approval ID: TAE000041N | | |

| | | EAC | | |
|--|--|---------------------------------|--|--|
| | | Approval ID: KZ7500651131219505 | | |

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PTT 1,5/S-2L BU - Feed-through terminal block

3210357

<https://www.phoenixcontact.com/us/products/3210357>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com