

0803467
<https://www.phoenixcontact.com/us/products/0803467>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Strip, white, labeled, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 8, text field height: 9.2 mm, text field width: 2.4 mm

Commercial data

Item number	0803467
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4055626074191
Weight per piece (including packing)	1.02 g
Weight per piece (excluding packing)	1.006 g
Customs tariff number	49119900
Country of origin	PL

TM-PTRV 4,QR:D-A - Marker for terminal blocks



0803467

<https://www.phoenixcontact.com/us/products/0803467>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	4 mm

Marking

Number of individual labels	8
-----------------------------	---

Dimensions

Width	2.40 mm
Height	25.99 mm
Depth	41.97 mm
Pitch	4 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PC

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

TM-PTRV 4,QR:D-A - Marker for terminal blocks



0803467

<https://www.phoenixcontact.com/us/products/0803467>

Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Mounting

Mounting type	latching
---------------	----------

TM-PTRV 4,QR:D-A - Marker for terminal blocks



0803467

<https://www.phoenixcontact.com/us/products/0803467>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

TM-PTRV 4,QR:D-A - Marker for terminal blocks



0803467
<https://www.phoenixcontact.com/us/products/0803467>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com