

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fabric label, Roll, white/black, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, roll length: 6 m, text field height: 10 mm, text field width: 6000 mm

Your advantages

- Enables labels to be stuck over edges and curves
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- The material is cUL certified
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- The label material consists of a textile foil with very low restoring forces
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon

Commercial data

Item number	0803934
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG241E
GTIN	4055626212142
Weight per piece (including packing)	54.5 g
Weight per piece (excluding packing)	51.6 g
Customs tariff number	96121010
Country of origin	CN

MM-EMLC (EX12)R C1 WH/BK - Fabric label

0803934

<https://www.phoenixcontact.com/us/products/0803934>



Technical data

Product properties

Product type	Gerätemarker
Marking	
Identification technology	Thermal transfer

Dimensions

Length of roll	6.00 m
Height	12 mm
Depth	0.12 mm

Material specifications

Foil strength	130 µm
Adhesive strength	28 µm
Adhesive	Acrylic
Color	multicolored (RAL -) white (RAL 9010) black (RAL 9005)
Base element material	PA
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S

MM-EMLC (EX12)R C1 WH/BK - Fabric label

0803934

<https://www.phoenixcontact.com/us/products/0803934>



Cycles	2
--------	---

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	0 °C ... 80 °C
Recommended storage conditions	5 - 35°C / 30 - 80 % relative humidity. Storage in a cool and dry place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	5 °C ... 35 °C
Recommended humidity (storage/transport)	30 % ... 80 %
Shelf life	24 months

Mounting

Mounting type	adhesive
---------------	----------

MM-EMLC (EX12)R C1 WH/BK - Fabric label

0803934

<https://www.phoenixcontact.com/us/products/0803934>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803934>



UL Recognized

Approval ID: MH48542-V2_S6

MM-EMLC (EX12)R C1 WH/BK - Fabric label

0803934

<https://www.phoenixcontact.com/us/products/0803934>



Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-EMLC (EX12)R C1 WH/BK - Fabric label

0803934

<https://www.phoenixcontact.com/us/products/0803934>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com