

PKE 9X20 - Marker sheet

0803980

<https://www.phoenixcontact.com/us/products/0803980>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker sheet, Sheet, white, unmarked, can be labeled with: CMS-P1-PLOTTER, mounting type: insert, cable diameter: > 10 mm, Number of individual labels: 20

Commercial data

Item number	0803980
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	BG20
Product key	BG2313
GTIN	4017918007874
Weight per piece (including packing)	22.517 g
Weight per piece (excluding packing)	22.517 g
Customs tariff number	39269097
Country of origin	IT

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	20
Number of individual labels per row	4

Dimensions

Width	20 mm
Depth	0.7 mm
Length	9 mm

Material specifications

Color	white (RAL 9010)
Material	ABS-PC
Flammability rating according to UL 94	V0
Components	halogen-free

Cable/line

External cable diameter	> 10.00 mm
-------------------------	------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

PKE 9X20 - Marker sheet



0803980

<https://www.phoenixcontact.com/us/products/0803980>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-50 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

PKE 9X20 - Marker sheet



0803980
<https://www.phoenixcontact.com/us/products/0803980>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

PKE 9X20 - Marker sheet



0803980
<https://www.phoenixcontact.com/us/products/0803980>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com