

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 1.5 m

## Your advantages

- Unshielded

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2299314                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C421                           |
| Product key                          | DK2211                         |
| GTIN                                 | 4017918886042                  |
| Weight per piece (including packing) | 106.8 g                        |
| Weight per piece (excluding packing) | 98.1 g                         |
| Customs tariff number                | 85444290                       |
| Country of origin                    | DE                             |

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                                         |                                          |
|---------------------------------------------------------|------------------------------------------|
| Degree of protection                                    | IP00                                     |
| Degree of protection (Installation location)            | ≥ IP54 (Installation location)           |
| Ambient temperature (operation) (fixed installation)    | -40 °C ... 70 °C (fixed installation)    |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport)                 | -40 °C ... 80 °C                         |
| Altitude                                                | ≤ 2000 m                                 |

### Electrical properties

|                          |                                  |
|--------------------------|----------------------------------|
| Operating voltage (AC)   | ≤ 30 V AC                        |
| Operating voltage (DC)   | ≤ 60 V DC                        |
| Nominal operating mode   | 100% operating factor            |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating)   |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

#### Supported controller EMERSON DeltaV

|                   |                       |
|-------------------|-----------------------|
| Suitable I/O card | VE4001S2T2B3          |
|                   | VE4001S2T2B3 Series 2 |
|                   | VE4001S2T1B3          |
|                   | VE4002S1T1B3          |
|                   | VE4002S1T2B3          |
|                   | VE4002S1T2B3 Series 2 |
|                   | VE4003S2B4            |
|                   | VE4005S2B3            |

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

#### 16X0.14 [PVC]

|                                 |                 |
|---------------------------------|-----------------|
| UL AWM Style                    | 2464/1061       |
| Number of positions             | 16              |
| Shielded                        | no              |
| Cable type                      | 16X0.14 [PVC]   |
| Conductor type                  | Round cable set |
| Conductor structure signal line | 7x 0.16 mm      |
| AWG signal line                 | 26              |
| Conductor cross section         | 16x 0.14 mm²    |
| Wire diameter incl. insulation  | 1 mm ±0.03 mm   |

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

|                                               |                                                                   |
|-----------------------------------------------|-------------------------------------------------------------------|
| External cable diameter                       | 6.80 mm ±0.4 mm                                                   |
| Outer sheath, material                        | Semi-rigid PVC                                                    |
| External sheath, color                        | gray                                                              |
| Conductor material                            | Tin-plated Cu litz wires                                          |
| Cable resistance                              | ≤ 145 Ω/km (20 °C)                                                |
| Insulation resistance                         | ≥ 20 MΩ*km (20 °C)                                                |
| Smallest bending radius, fixed installation   | 58 mm                                                             |
| Smallest bending radius, movable installation | 108 mm                                                            |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |
| Halogen-free                                  | no                                                                |
| Flame resistance                              | IEC 60332-1-2 (raw cable)                                         |
|                                               | VDE 0842, Part 332-1-2 (raw cable)                                |
|                                               | IEC 60332-3-22 (raw cable)                                        |
|                                               | UL VW-1                                                           |
|                                               | CSA FT-1                                                          |
| Resistance to oil                             | can withstand occasional splashes (raw cable)                     |
| Cable type                                    | Cable for one module                                              |

Color code: Single-core wire

|              |                                 |
|--------------|---------------------------------|
| black        | IDC/FLK16 (1) = IDC/FLK16 (1)   |
| brown        | IDC/FLK16 (2) = IDC/FLK16 (2)   |
| red          | IDC/FLK16 (3) = IDC/FLK16 (3)   |
| orange       | IDC/FLK16 (4) = IDC/FLK16 (4)   |
| yellow       | IDC/FLK16 (5) = IDC/FLK16 (5)   |
| green        | IDC/FLK16 (6) = IDC/FLK16 (6)   |
| blue         | IDC/FLK16 (7) = IDC/FLK16 (7)   |
| violet       | IDC/FLK16 (8) = IDC/FLK16 (8)   |
| gray         | IDC/FLK16 (9) = IDC/FLK16 (9)   |
| white        | IDC/FLK16 (10) = IDC/FLK16 (10) |
| white-black  | IDC/FLK16 (11) = IDC/FLK16 (11) |
| white-brown  | IDC/FLK16 (12) = IDC/FLK16 (12) |
| white-red    | IDC/FLK16 (13) = IDC/FLK16 (13) |
| white-orange | IDC/FLK16 (14) = IDC/FLK16 (14) |
| white-yellow | IDC/FLK16 (15) = IDC/FLK16 (15) |
| white-green  | IDC/FLK16 (16) = IDC/FLK16 (16) |

## Connection data

Connection 1

|                                  |                              |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method                | IDC/FLK socket strip         |
| Number of connections            | 1                            |
| Number of positions              | 16                           |
| Insertion/withdrawal cycles      | > 50                         |

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

|       |         |
|-------|---------|
| Pitch | 2.54 mm |
|-------|---------|

## Connection 2


|                                  |                              |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method                | IDC/FLK socket strip         |
| Number of connections            | 1                            |
| Number of positions              | 16                           |
| Insertion/withdrawal cycles      | > 50                         |
| Pitch                            | 2.54 mm                      |

## Notes

|                    |                                                                                                                                                                                                                                                                                |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Drawings

Diagram



Maximum permissible current per path in uncoiled state

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2299314>



**EAC**

Approval ID: RU\*-DE.HB\*35.B00385



**UL Listed**

Approval ID: E238705

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 125 V                 | 1 A                   | -                 | -                           |



**cUL Listed**

Approval ID: E238705

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 125 V                 | 1 A                   | -                 | -                           |

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242220 |
| ECLASS-15.0 | 27242220 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000237 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# FLK 16/EZ-DR/ 150/KONFEK - Cable



2299314

<https://www.phoenixcontact.com/us/products/2299314>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)