

GW PL DP/MODBUS - Protocol converter

2316365

<https://www.phoenixcontact.com/us/products/2316365>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modbus/RTU to PROFIBUS DP protocol converter

Product description

Protocol converter capable of connecting four Modbus/RTU devices to a PROFIBUS DP network

Commercial data

Item number	2316365
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC135
GTIN	4055626127378
Weight per piece (including packing)	217 g
Weight per piece (excluding packing)	216 g
Customs tariff number	85176200
Country of origin	US

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Interface converter
--------------	---------------------

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Supply

Supply voltage range	18 V DC ... 30 V DC
Nominal supply voltage	24 V DC
Max. current consumption	60 mA

Connection data

Supply

Connection method	COMBICON plug-in screw terminal block
Conductor cross-section, flexible	0.20 mm² ... 2.50 mm²
Conductor cross-section, rigid	0.20 mm² ... 2.50 mm²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Interfaces

Signal	Modbus
--------	--------

Data: PROFIBUS DP

Data rate	9.6 kbps (min.)
	12 Mbps (max.)
Number of connections	2
Connection method	D-SUB-9, COMBICON
No. of channels	1
Tightening torque	0.5 Nm ... 0.6 Nm
Connection technology	Screw connection
Termination resistor	390 Ω - 220 Ω - 390 Ω (switchable)
Conductor cross-section flexible max.	2.5 mm²

GW PL DP/MODBUS - Protocol converter



2316365


<https://www.phoenixcontact.com/us/products/2316365>

Conductor cross-section flexible min.	0.2 mm²
Conductor cross-section, rigid max.	2.5 mm²
Conductor cross-section, rigid min.	0.2 mm²
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24
Protocols supported	Modbus/RTU, PROFIBUS DP

Data: Modbus/RTU

Transmission speed	1200 kbps (min.)
Data rate	115.2 kbps (max.)
Number of connections	2
Connection method	COMBICON
No. of channels	4 (Modbus/RTU devices)
Tightening torque	0.5 Nm ... 0.6 Nm
Connection technology	Screw connection
Termination resistor	Switchable
Conductor cross-section flexible max.	2.5 mm²
Conductor cross-section flexible min.	0.2 mm²
Conductor cross-section, rigid max.	2.5 mm²
Conductor cross-section, rigid min.	0.02 mm²
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24

Dimensions

Dimensional drawing	
Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Material specifications

Color	gray
Housing material	PA V0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Altitude	2000 m
Permissible humidity (operation)	95 % (non-condensing)
Shock	30g, 18 ms
Vibration (operation)	10 Hz ... 150 Hz, 5g

Approvals

Ex data

ATEX	PRESAFE 16ATEX7686X, II 3G, Ex nA IIC T4 Gc
IECEX	IECEX PRE 16.0001X, Ex nA IIC T4 Gc
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D Class I, Zone 2, AEx nA IIC T4, Ex nA IIC T4 GcX

Standards and regulations

Standards/regulations	IEC 60079-15
	IEC 60079-0

Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715
Useable DIN rail type	DIN rail: 35 mm


GW PL DP/MODBUS - Protocol converter

2316365


<https://www.phoenixcontact.com/us/products/2316365>



Drawings



Block diagram



GW PL DP/MODBUS - Protocol converter



2316365

<https://www.phoenixcontact.com/us/products/2316365>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2316365>



IECEx

Approval ID: IECEx PRE 16.0001X



cUL Listed

Approval ID: E199827



UL Listed

Approval ID: E199827



ATEX

Approval ID: Presafe 16ATEX7686X

Classifications

ECLASS

ECLASS-13.0	27242208
ECLASS-15.0	27242208

ETIM

ETIM 9.0	EC001423
----------	----------

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%