

# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Siren element, 24 V AC/DC, max. 105 db(A), continuous tone and alternating continuous tone

## Product description

This audible signal element is designed as a component of a modular signal tower. According to your requirements, a signal tower may comprise any combination of up to five signal elements. You may use up to five optical signal elements or up to four optical and one audible signal element. Only use an audible signal element as the top element. A bayonet locking system establishes the mechanical and electrical connection between the elements. Connection elements with spring-cage or screw connection can be used for electrical connection of the signal tower. Mounting elements for base or tube mounting can be used to mount the signal tower. Please note that PSD-S signal towers (70 mm diameter) are not mechanically compatible with PSD-S 50 signal towers (50 mm diameter).

## Your advantages

- Multi-tone siren signaling depending on the situation
- Two tone functions can be selected via DIP switches
- Adjustable volume
- Degree of protection: IP65, when mounted

## Commercial data

Item number	2702998
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL113
GTIN	4055626492070
Weight per piece (including packing)	87 g
Weight per piece (excluding packing)	87 g
Customs tariff number	85318070
Country of origin	DE

# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

Product type	Signal element
Product family	PSD-S

### Electrical properties

#### General

Input voltage	24 V AC/DC $\pm 10\%$
Nominal input voltage range	21.6 V AC/DC ... 26.4 V AC/DC
Maximum inrush current	max. 100 mA
Current consumption	typ. 80 mA
Operating time	100 %
Service life electrical	min. 5,000 h
Type of acoustic signal	Continuous tone Alternating continuous tone
Tone frequency	3 kHz (Continuous tone)
Volume	max. 105 dB

### Dimensions

Dimensional drawing	
Height	54 mm
Diameter	70 mm

### Material specifications

Color	black
Material	Polycarbonate PC

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65, when installed
Ambient temperature (operation)	-30 °C ... 50 °C

# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Mounting

Mounting type	Plug-in mounting
Mounting position	any

# PSD-S AE SM2-7 105DB/1 - Acoustic element


2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Drawings

Dimensional drawing



# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702998>



**cULus Listed**

Approval ID: E123528

# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Classifications

### ECLASS

ECLASS-13.0	27371237
ECLASS-15.0	27371237

### ETIM

ETIM 9.0	EC001261
----------	----------

### UNSPSC

UNSPSC 21.0	46171600
-------------	----------

# PSD-S AE SM2-7 105DB/1 - Acoustic element

2702998

<https://www.phoenixcontact.com/us/products/2702998>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2) Lead(CAS: 7439-92-1)
SCIP	9302a92c-ff4f-41c3-a36c-9515ca2868bc

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)