

# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection, consisting of protective plug and base element, with integrated status indicator for two signal wires with common reference potential, e.g., Digital IN/OUT. Can be used in safety-related circuits up to SIL 3.

## Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Continuous monitoring of protective devices, plus mechanical status indicator with optional remote signaling
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features
- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2906816       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL23          |
| Product key                          | CL2162        |
| GTIN                                 | 4055626135793 |
| Weight per piece (including packing) | 41.371 g      |
| Weight per piece (excluding packing) | 35.19 g       |
| Customs tariff number                | 85363010      |
| Country of origin                    | DE            |

# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## Technical data

### Product properties

|                         |                                         |
|-------------------------|-----------------------------------------|
| Product type            | Surge protection for MCR technology     |
| Product family          | TERMITRAB complete                      |
| IEC test classification | C1                                      |
|                         | C2                                      |
|                         | C3                                      |
|                         | D1                                      |
| Type                    | DIN rail module, two-section, divisible |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |


### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 24 V DC |
|-----------------------|---------|

### Connection data

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection method                | Push-in connection                          |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section AWG      | 24 ... 12                                   |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 6.2 mm +0.1 mm                                                                       |
| Height              | 105.8 mm                                                                             |
| Depth               | 100 mm (incl. DIN rail 7.5 mm)                                                       |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color (Base element)                   | gray (RAL 7042)       |
| Color (Male connector)                 | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V-0                   |
| Insulating material                    | PBT                   |
| Housing material                       | PBT                   |

### Mechanical properties

#### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## Protective circuit

|                                                                   |                                                                                    |
|-------------------------------------------------------------------|------------------------------------------------------------------------------------|
| Direction of action                                               | Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground |
| Maximum continuous operating voltage $U_C$                        | 30 V DC                                                                            |
|                                                                   | 21 V AC                                                                            |
| Rated current                                                     | 600 mA (56 °C)                                                                     |
| Operating effective current $I_C$ at $U_C$                        | $\leq 5 \mu A$                                                                     |
| Protective conductor current $I_{PE}$                             | $\leq 10 \mu A$                                                                    |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (line-ground)      | 5 kA                                                                               |
| Pulse discharge current $I_{imp}$ (10/350) $\mu s$ (line-earth)   | 0.5 kA                                                                             |
| Total discharge current $I_{Total}$ (8/20) $\mu s$                | 10 kA                                                                              |
| Voltage protection level $U_p$ (line-earth)                       | $\leq 140 V$ (C1 - 1 kV / 500 A)                                                   |
|                                                                   | $\leq 190 V$ (C2 - 10 kV / 5 kA)                                                   |
|                                                                   | $\leq 45 V$ (C3 - 25 A)                                                            |
|                                                                   | $\leq 50 V$ (C3 - 100 A)                                                           |
| Voltage protection level $U_p$ static (line-earth)                | $\leq 55 V$ (C1 - 1 kV / 500 A)                                                    |
|                                                                   | $\leq 120 V$ (C2 - 10 kV / 5 kA)                                                   |
| Response time $t_A$ (line-earth)                                  | $\leq 1 ns$                                                                        |
| Input attenuation aE, asym.                                       | typ. 0.3 dB ( $\leq 270 kHz/150 \Omega$ )                                          |
| Cut-off frequency $f_g$ (3 dB), asym. (PE) in 150 $\Omega$ system | typ. 960 kHz                                                                       |
| Capacity (Core-Earth)                                             | typ. 2.2 nF                                                                        |
| Resistance per path                                               | 1.65 $\Omega \pm 20 \%$                                                            |
| Surge protection fault message                                    | optical                                                                            |
| Max. required back-up fuse                                        | 630 mA (FF)                                                                        |
| Impulse durability (line-earth)                                   | C1 - 1 kV / 500 A                                                                  |
|                                                                   | C2 - 10 kV / 5 kA                                                                  |
|                                                                   | C3 - 100 A                                                                         |
|                                                                   | D1 - 500 A                                                                         |
| Pulse reset time (line-earth)                                     | $\leq 300 ms$                                                                      |

## Additional technical data

|                                                             |            |
|-------------------------------------------------------------|------------|
| Max. total discharge current $I_{total max}$ (8/20) $\mu s$ | 20 kA (1x) |
|-------------------------------------------------------------|------------|

## Environmental and real-life conditions

### Ambient conditions

|                                         |                      |
|-----------------------------------------|----------------------|
| Degree of protection                    | IP20                 |
| Ambient temperature (operation)         | -40 °C ... 85 °C     |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C     |
| Altitude                                | $\leq 4000 m$ (amsl) |
| Permissible humidity (operation)        | 5 % ... 95 %         |

## Standards and regulations

|                          |                                                       |
|--------------------------|-------------------------------------------------------|
| Standards/specifications | IEC 61643-21                                          |
| Note                     | 2000 + corrigendum 2001 + A1:2008, modified + A2:2012 |

# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## EN 61643-21

|                          |                          |
|--------------------------|--------------------------|
| Standards/specifications | EN 61643-21              |
| Note                     | 2001 + A1:2009 + A2:2013 |

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | DIN rail: TH 35 - 7.5 mm |
|---------------|--------------------------|


TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816  
https://www.phoenixcontact.com/us/products/2906816

Drawings

Dimensional drawing




Schematic diagram

| TTC-6P-2X1-...-I                                                                                                                                                                 |                                  |                                      |                          |       |                                  |                                       |      |                          |       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|--------------------------------------|--------------------------|-------|----------------------------------|---------------------------------------|------|--------------------------|-------|
| Category                                                                                                                                                                         | 1oo1 architecture, HFT=0         |                                      |                          |       | 1oo2 architecture, HFT=1         |                                       |      |                          |       |
|                                                                                                                                                                                  | PFD <sub>AVG</sub>               | PFH                                  | Used budget of SIL 2 SIF |       | PFD <sub>AVG</sub>               | PFH                                   | CCF  | Used budget of SIL 3 SIF |       |
|                                                                                                                                                                                  |                                  |                                      | PFD <sub>AVG</sub>       | PFH   |                                  |                                       |      | PFD <sub>AVG</sub>       | PFH   |
|                                                                                                                                                                                  |                                  |                                      |                          |       |                                  |                                       |      |                          |       |
|                                                                                                                                                                                  | 1.69 <sub>x10<sup>-5</sup></sub> | 3.00 <sub>x10<sup>-9</sup></sub> 1/h | 0.2 %                    | 0.3 % | 8.44 <sub>x10<sup>-7</sup></sub> | 1.50 <sub>x10<sup>-10</sup></sub> 1/h | 5 %  | 0.1 %                    | 0.2 % |
|                                                                                                                                                                                  |                                  |                                      |                          |       | 1.69 <sub>x10<sup>-6</sup></sub> | 3.00 <sub>x10<sup>-10</sup></sub> 1/h | 10 % | 0.2 %                    | 0.3 % |
| Calculation based on exida report, Phoenix Contact 16/06-072 R022 V4R2<br>exida Profile 1, FMEDA Analysis 2, T <sub>proof</sub> : 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99% |                                  |                                      |                          |       |                                  |                                       |      |                          |       |
| Used standards<br>IEC/EN 61508, edition 2010 (device specific)<br>IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific)                                             |                                  |                                      |                          |       |                                  |                                       |      |                          |       |

Functional safety scenarios

Diagram




# TTC-6P-2X1-24DC-PT-I - Surge protection device

2906816

<https://www.phoenixcontact.com/us/products/2906816>



Circuit diagram



# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906816>



**CSA**

Approval ID: 70136717



**DNV GL**

Approval ID: TAE000027G



**UL Listed**

Approval ID: FILE E 138168



**CSAus**

Approval ID: 70136717

**UAE-RoHS**

Approval ID: 22-06-16781

**Functional Safety**

Approval ID: 16-06-072 R022 V4R3

# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171501 |
| ECLASS-15.0 | 27171501 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000943 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|



# TTC-6P-2X1-24DC-PT-I - Surge protection device



2906816

<https://www.phoenixcontact.com/us/products/2906816>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 7b3ed623-0236-4eaf-834a-faef7e3a514d |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)