

FLX-D37F/32CH/DI/TDC3K - Termination board



2908889

<https://www.phoenixcontact.com/us/products/2908889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Migration board for converting TDC3000 to modern control platforms, digital input, 32 channel

Your advantages

- Panel mount to existing TDC3000 chassis
- Compatible with existing pluggable field wiring connectors
- DSUB control side connection
- Terminal blocks for power supply

Commercial data

Item number	2908889
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C421
Product key	DK2B8H
GTIN	4055626733067
Weight per piece (including packing)	577.5 g
Weight per piece (excluding packing)	550 g
Customs tariff number	85371098
Country of origin	US

Technical data

Product properties

Product type	Interface module
Insulation characteristics	
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. operating voltage $U_{\max}$	30 V DC (Power supply)
Operating voltage	30 V DC
Max. current carrying capacity per branch	500 mA
Maximum power voltage feed	5 A (fuse limited)

Supported controller HONEYWELL TDC3000

Suitable I/O card	TDIY22
-------------------	--------

Connection data

Controller level

Connection method	D-SUB 37 female connector
Number of connections	2
Number of positions	37

Field level

Connection method	pluggable
-------------------	-----------

Dimensions

Item dimensions

Width	307.3 mm
Height	120.7 mm
Depth	38.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Altitude	< 2000 m
Permissible humidity (operation)	< 90 %

Mounting

Mounting type	TDC3000 chassis
Mounting position	any

FLX-D37F/32CH/DI/TDC3K - Termination board



2908889

<https://www.phoenixcontact.com/us/products/2908889>

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLX-D37F/32CH/DI/TDC3K - Termination board





2908889


<https://www.phoenixcontact.com/us/products/2908889>

Drawings

Dimensional drawing



Circuit diagram



FLX-D37F/32CH/DI/TDC3K - Termination board



2908889

<https://www.phoenixcontact.com/us/products/2908889>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908889>

CSA Approval ID: 108860_0_000				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

cUL Recognized Approval ID: NRAQ8.E238705				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

UL Recognized Approval ID: NRAQ2 - E238705				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

CSAus Approval ID: 108860_0_000				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

FLX-D37F/32CH/DI/TDC3K - Termination board



2908889

<https://www.phoenixcontact.com/us/products/2908889>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLX-D37F/32CH/DI/TDC3K - Termination board



2908889

<https://www.phoenixcontact.com/us/products/2908889>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7fccf92c-56b8-424f-9a70-afd5cda3958b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com