

PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface module for connecting several safety sensors or switches with N/C / N/O contacts to the PSR-SDC4 safety relay, plug-in Push-in terminal blocks

Your advantages

- 4 two-channel N/O or N/C contact inputs
- Up to Cat. 3/PL d in accordance with EN ISO 13849-1, SIL 2 in accordance with IEC 61508 (in conjunction with the PSR-SDC4 master)
- 4 PLC diagnostic outputs for evaluating the switching state of the safety sensors
- 4 LEDs as status indicators for the relevant sensor/switch
- PSR-TBUS connection

Commercial data

Item number	2981949
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA221
GTIN	4046356325998
Weight per piece (including packing)	175 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Interface module
Product family	PSRclassic

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Max. permissible current	100 mA (per signal output)
Max. permissible total current	100 mA (alarm outputs)
Nominal operating mode	100% operating factor
Rated insulation voltage	50 V DC
Rated surge voltage	0.8 kV

Input data

Nominal input voltage U_N	24 V DC (from PSR)
Input voltage range in reference to U_N	0.85 ... 1.1
Nominal input voltage U_N	24 V DC (from PSR)

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Signaling

Status display	LED (green)
Status display present	yes

PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Dimensions

Width	22.5 mm
Height	117 mm
Depth	106 mm

Material specifications

Housing material	PA
------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	max. 2000 m (Above sea level)

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

PSR-SPP- 24DC/SIM4 - Safety relays


2981949

<https://www.phoenixcontact.com/us/products/2981949>



Drawings

Application drawing



Up to 4 safety door switches can be connected to one PSR-SIM4.


PSR-SPP- 24DC/SIM4 - Safety relays



2981949


<https://www.phoenixcontact.com/us/products/2981949>

Application drawing



Additional inputs are aligned on the left of the PSR-SDC4, outputs are to its right.

Circuit diagram



Block diagram


PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Circuit diagram



Contact extension

PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2981949>



cULus Listed

Approval ID: E140324

PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Classifications

ECLASS

ECLASS-13.0	27371819
ECLASS-15.0	27371819

ETIM

ETIM 9.0	EC001449
----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

PSR-SPP- 24DC/SIM4 - Safety relays



2981949

<https://www.phoenixcontact.com/us/products/2981949>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	02fe4f76-9c2e-4db0-bebb-7a77c349bc39

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com