

UC-PMP (110X38) - Insert label

0831019

<https://www.phoenixcontact.com/us/products/0831019>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: snapped into marker carrier, Number of individual labels: 1, text field height: 38 mm, text field width: 110 mm



Your advantages

- The UC-PMP ... plant identification family includes markers that can be mounted in existing CARRIER..-PMP... marker carriers
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0831019
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2617
GTIN	4046356940481
Weight per piece (including packing)	10.321 g
Weight per piece (excluding packing)	9.127 g
Customs tariff number	39269097
Country of origin	PL

UC-PMP (110X38) - Insert label

0831019

<https://www.phoenixcontact.com/us/products/0831019>



Technical data

Product properties

Product type	Plant marker
Marking	
Number of individual labels	1
Identification technology	UV LED technology

Dimensions

Width	110.00 mm
Height	38.00 mm
Depth	1.15 mm

Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

UC-PMP (110X38) - Insert label

0831019

<https://www.phoenixcontact.com/us/products/0831019>



Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Standards	
Standards/regulations	EN 45545-2

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

UC-PMP (110X38) - Insert label

0831019

<https://www.phoenixcontact.com/us/products/0831019>



Classifications

ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-PMP (110X38) - Insert label

0831019

<https://www.phoenixcontact.com/us/products/0831019>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.078 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com