

UCT-WMCO 5,4 (23X8) - Wire marking



0832105

<https://www.phoenixcontact.com/us/products/0832105>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, cable diameter range: 4.7 ... 5.4 mm, mounting type: clip on, Number of individual labels: 18, text field height: 8 mm, text field width: 23 mm

Your advantages

- The UCT-WMCO ... UniCard labeling range includes markers for the subsequent labeling of conductors by simply snapping on
- Large-surface labeling option in a space-saving design
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- Secure tight fit even in the event of vibrations
- The format automatically ensures printing with a high degree of positioning accuracy

Commercial data

Item number	0832105
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG10
Product key	BG2218
GTIN	4055626258645
Weight per piece (including packing)	15.72 g
Weight per piece (excluding packing)	15.72 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	18
Number of individual labels per row	6

Dimensions

Width	23 mm
Height	8.6 mm
Depth	8.59 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V0
Base element material	PC
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	4.7 mm ... 5.4 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesa film test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

UCT-WMCO 5,4 (23X8) - Wire marking



0832105

<https://www.phoenixcontact.com/us/products/0832105>

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

UCT-WMCO 5,4 (23X8) - Wire marking



0832105

<https://www.phoenixcontact.com/us/products/0832105>

Mounting type	clip on
---------------	---------

UCT-WMCO 5,4 (23X8) - Wire marking



0832105

<https://www.phoenixcontact.com/us/products/0832105>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-WMCO 5,4 (23X8) - Wire marking



0832105

<https://www.phoenixcontact.com/us/products/0832105>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.068 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com