

# TMC 71B 01A - Miniature Circuit Breaker



1011962

<https://www.phoenixcontact.com/us/products/1011962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic Miniature Circuit Breaker, 1-position, use: Supplementary Protection (UL 1077), for protection against overload up to a short-circuit current of 7.5 kA, tripping characteristic: B, mounting type: NS 35/..., rated current: 1 A

## Your advantages

- Can be used worldwide due to international approvals
- Suitable for various grid types, as it is available in 1-, 2-, 3-pos. versions
- Ideally coordinated protection due to various tripping characteristics and a wide selection of nominal currents
- Reduced inventory because of suitability for AC and DC applications
- Optional accessories enable remote control and monitoring

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1011962       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL09          |
| Product key                          | CLA126        |
| GTIN                                 | 4055626487502 |
| Weight per piece (including packing) | 113,300 g     |
| Customs tariff number                | 85362010      |
| Country of origin                    | CN            |

# TMC 71B 01A - Miniature Circuit Breaker



1011962

<https://www.phoenixcontact.com/us/products/1011962>

## Technical data

### Product properties

|                         |                                                                                                                              |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Product type            | Circuit breakers                                                                                                             |
| Product family          | TMC 7                                                                                                                        |
| Type                    | DIN rail module, one-piece                                                                                                   |
| Number of positions     | 1                                                                                                                            |
| Mechanical service life | 20000                                                                                                                        |
| Special properties      | Supplementary Protection (UL 1077), for protection against overload up to a short-circuit current of 7.5 kA Thermal-magnetic |

### Electrical properties

|                         |      |
|-------------------------|------|
| Service life electrical | 6000 |
|-------------------------|------|

### General

|                                                 |                            |
|-------------------------------------------------|----------------------------|
| Operating voltage                               | 277 V AC                   |
|                                                 | 60 V DC                    |
| Rated current $I_N$                             | 1 A                        |
| Tripping method                                 | TM (thermal-magnetic)      |
| Rated short-circuit switching capacity $I_{cn}$ | 7.5 kA (240 V AC/ 60 V DC) |
|                                                 | 5 kA (277 V AC)            |
| Fuse                                            | B                          |
| Contact switching type                          | none                       |

### Connection data

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| Conductor cross-section rigid         | 1 mm <sup>2</sup> ... 35 mm <sup>2</sup> |
| Cross section AWG                     | 18 ... 2 (converted acc. to IEC)         |
| Conductor cross-section flexible      | 1 mm <sup>2</sup> ... 35 mm <sup>2</sup> |
| Connection method                     | Screw connection                         |
| Tightening torque, min                | 2 Nm                                     |
| Stripping length                      | 11 mm ... 12 mm                          |
| Conductor cross-section flexible max. | 35 mm <sup>2</sup>                       |
| Conductor cross-section, rigid max.   | 35 mm <sup>2</sup>                       |

### Dimensions

|                     |                                 |
|---------------------|---------------------------------|
| Dimensional drawing |                                 |
| Width               | 17.6 mm                         |
| Height              | 84.3 mm                         |
| Depth               | 75.9 mm (incl. DIN rail 7.5 mm) |

# TMC 71B 01A - Miniature Circuit Breaker



1011962

<https://www.phoenixcontact.com/us/products/1011962>

## Material specifications

|       |                       |
|-------|-----------------------|
| Color | light gray (RAL 7035) |
|-------|-----------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                                                                                                                             |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Degree of protection            | IP20                                                                                                                        |
| Ambient temperature (operation) | -35 °C ... 70 °C                                                                                                            |
| Humidity test                   | 48 h, 95% RH, 40°C (IEC 60068-2-78)                                                                                         |
| Shock (operation)               | 30g (11 ms) (IEC 60068-2-11, test Ea)                                                                                       |
| Vibration (operation)           | ±0.38 mm (10 Hz ... 57 Hz), 5g (57 Hz ... 500 Hz) (Sinusoidal test to IEC 60068-2-6, Test Fc. 10 frequency cycles per axis) |

## Standards and regulations

|                          |             |
|--------------------------|-------------|
| Standards/specifications | UL 1077     |
| Standards/specifications | IEC 60947-2 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/... |
|---------------|-----------|

# TMC 71B 01A - Miniature Circuit Breaker




1011962


<https://www.phoenixcontact.com/us/products/1011962>

## Drawings

Dimensional drawing



Diagram



# TMC 71B 01A - Miniature Circuit Breaker



1011962

<https://www.phoenixcontact.com/us/products/1011962>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1011962>



**cUL Recognized**

Approval ID: FILE E 140459



**UL Recognized**

Approval ID: FILE E 140459



**TÜV Rheinland**

Approval ID: R 50531587



**CCC**

Approval ID: 2024010307673885

# TMC 71B 01A - Miniature Circuit Breaker



1011962

<https://www.phoenixcontact.com/us/products/1011962>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003538 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121410 |
|-------------|----------|

# TMC 71B 01A - Miniature Circuit Breaker



1011962  
<https://www.phoenixcontact.com/us/products/1011962>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 2.045 kg CO2e                            |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)