

# UCT-WMTBA (29X6) YE - Cable marker



1014085

<https://www.phoenixcontact.com/us/products/1014085>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Sheet, yellow, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: Assembly with cable ties, cable diameter: > 6 mm, Number of individual labels: 12, text field height: 6 mm, text field width: 29 mm



## Your advantages

- The UCT-WMTBA ... UniCard labeling range includes markers that can be secured using standard cable binders
- Thanks to their angular shape the markers fit perfectly onto cables
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	1014085
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2318
GTIN	4046356781374
Weight per piece (including packing)	10.08 g
Weight per piece (excluding packing)	10 g
Customs tariff number	39269097
Country of origin	PL

# UCT-WMTBA (29X6) YE - Cable marker

1014085

<https://www.phoenixcontact.com/us/products/1014085>



## Technical data

### Product properties

Product type	Conductor marker
Marking	
Number of individual labels	12
Number of individual labels per row	4

### Dimensions

Width	29.9 mm
Height	9.87 mm
Depth	4.05 mm

### Material specifications

Color	yellow (RAL 1018)
Flammability rating according to UL 94	V0
Base element material	PC
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

### Cable/line

External cable diameter	> 6.00 mm
-------------------------	-----------

### Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish	
Result	Test passed

Test for substances that would hinder coating with paint or varnish	
Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test	
Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance	
Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

# UCT-WMTBA (29X6) YE - Cable marker

1014085

<https://www.phoenixcontact.com/us/products/1014085>



## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

## Standards and regulations

Standards	
Standards/regulations	EN 45545-2

# UCT-WMTBA (29X6) YE - Cable marker

1014085

<https://www.phoenixcontact.com/us/products/1014085>



## Mounting

Mounting type

Assembly with cable ties

# UCT-WMTBA (29X6) YE - Cable marker

1014085

<https://www.phoenixcontact.com/us/products/1014085>



## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UCT-WMTBA (29X6) YE - Cable marker

1014085

<https://www.phoenixcontact.com/us/products/1014085>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.044 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)