

# WT-STEEL SH 7,9X259 - Cable tie

3240827

<https://www.phoenixcontact.com/us/products/3240827>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, made from rust-free stainless steel (AISI 316), suitable for the harshest of ambient conditions (for example, salt water), with ball lock, for quick and secure bundling and fastening

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240827       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE07          |
| Product key                          | BE7132        |
| GTIN                                 | 4046356705752 |
| Weight per piece (including packing) | 5.893 g       |
| Weight per piece (excluding packing) | 5.893 g       |
| Customs tariff number                | 73269098      |
| Country of origin                    | GB            |

# WT-STEEL SH 7,9X259 - Cable tie

3240827

<https://www.phoenixcontact.com/us/products/3240827>



## Technical data

### Product properties

|                      |           |
|----------------------|-----------|
| Product type         | Cable tie |
| Tensile strength GRP | 1335 N    |

### Dimensions

|                         |         |
|-------------------------|---------|
| Width                   | 7.9 mm  |
| Length                  | 259 mm  |
| Max. material thickness | 0.25 mm |

### Material specifications

|            |                                 |
|------------|---------------------------------|
| Color      | silver-colored                  |
| Material   | Stainless steel 1.4401/AISI 316 |
| Components | free from silicone and halogen  |

### Cable/line

|                         |            |
|-------------------------|------------|
| External cable diameter | ≤ 69.00 mm |
| Tensile strength        | 1335 N     |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -80 °C ... 538 °C |
| Ambient temperature (assembly)  | -80 °C ... 538 °C |
| Resistance to UV radiation      | yes               |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-STEEL SH 7,9X259 - Cable tie



3240827

<https://www.phoenixcontact.com/us/products/3240827>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240827>



**cULus Listed**

Approval ID: E328576

# WT-STEEL SH 7,9X259 - Cable tie

3240827

<https://www.phoenixcontact.com/us/products/3240827>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140702 |
| ECLASS-15.0 | 27140702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-STEEL SH 7,9X259 - Cable tie



3240827

<https://www.phoenixcontact.com/us/products/3240827>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)