

WP-PA HF-SL 21,2 BK - Protective hose



3240845

<https://www.phoenixcontact.com/us/products/3240845>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: PA, UV-resistant: yes, flexible, degree of protection: IP40, color: black, flammability rating in acc. with UL 94: HB, inside diameter: 16.5 mm, Total length: 10 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240845 |
| Packing unit | 1 m |
| Minimum order quantity | 10 m |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356736619 |
| Weight per piece (including packing) | 999.9 g |
| Weight per piece (excluding packing) | 8,460 g |
| Customs tariff number | 39173200 |
| Country of origin | DE |

WP-PA HF-SL 21,2 BK - Protective hose



3240845

<https://www.phoenixcontact.com/us/products/3240845>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | Protective hose length is measured stretched out; length tolerance $\pm 5\%$ |
|--------------------|--|

Product properties

| | |
|----------------------|-----------------|
| Product type | Protective hose |
| Tensile strength GRP | 100 N |

Dimensions

External dimensions

| | |
|------------------|---------|
| Outside diameter | 21.2 mm |
|------------------|---------|

Internal dimensions

| | |
|-------------------|---------|
| Internal diameter | 16.5 mm |
|-------------------|---------|

Material specifications

| | |
|--|--|
| Material | PA |
| Flammability rating according to UL 94 | HB |
| Components | free from silicone, halogen, and cadmium |

Cable/line

| | |
|-------------------------|--------|
| Bending radius, dynamic | 120 mm |
| Bending radius, static | 40 mm |
| Tensile strength | 100 N |
| Halogen-free | yes |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP40 |
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Resistance to UV radiation | yes |
| Short-term temperature | 120 °C |

WP-PA HF-SL 21,2 BK - Protective hose



3240845

<https://www.phoenixcontact.com/us/products/3240845>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240845>



UL Recognized
Approval ID: E86359

WP-PA HF-SL 21,2 BK - Protective hose



3240845

<https://www.phoenixcontact.com/us/products/3240845>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27430304 |
| ECLASS-15.0 | 27430304 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001177 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 40141700 |
|-------------|----------|

WP-PA HF-SL 21,2 BK - Protective hose



3240845

<https://www.phoenixcontact.com/us/products/3240845>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com