

# BMKL 19X11 YE - Label sheet, DIN A4



0800705

<https://www.phoenixcontact.com/us/products/0800705>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, yellow, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 168, text field height: 11 mm, text field width: 19 mm



## Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0800705       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG13          |
| Product key                          | BG2414        |
| GTIN                                 | 4017918104047 |
| Weight per piece (including packing) | 14.26 g       |
| Weight per piece (excluding packing) | 14.26 g       |
| Customs tariff number                | 39199080      |
| Country of origin                    | DE            |

## Technical data

### Notes

|         |                                                 |
|---------|-------------------------------------------------|
| General | Print image may vary depending on laser printer |
|---------|-------------------------------------------------|

### Product properties

|              |              |
|--------------|--------------|
| Product type | Gerätemarker |
|--------------|--------------|

### Marking

|                                     |                       |
|-------------------------------------|-----------------------|
| Number of individual labels         | 168                   |
| Number of individual labels per row | 7                     |
| Identification technology           | Office laser printing |

### Dimensions

|        |          |
|--------|----------|
| Width  | 11.00 mm |
| Height | 19.00 mm |
| Depth  | 0.09 mm  |

### Material specifications

|                       |                   |
|-----------------------|-------------------|
| Color                 | yellow (RAL 1018) |
| Material              | Polyester         |
| Base element material | Polyester         |
| Components            | Silicone-free     |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|               |                                       |
|---------------|---------------------------------------|
| Result        | Test passed                           |
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements  | ≥ 5 N                                 |
| Result        | Test passed                           |

#### Tesafilm test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |
| Procedure     | Artificial irradiation.        |

#### Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

# BMKL 19X11 YE - Label sheet, DIN A4



0800705

<https://www.phoenixcontact.com/us/products/0800705>

## Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                  |
|-----------------------------------------------------|------------------|
| Ambient temperature (operation)                     | -20 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 20 °C ... 25 °C  |
| Recommended humidity (storage/transport)            | 40 % ... 50 %    |
| Shelf life                                          | 2 years          |

## Standards and regulations


|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

## Drawings

## Dimensional drawing



# BMKL 19X11 YE - Label sheet, DIN A4



0800705

<https://www.phoenixcontact.com/us/products/0800705>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

0800705

<https://www.phoenixcontact.com/us/products/0800705>

Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)