

# THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 64 mm, color: black

## Commercial data

Item number	0801360
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4046356632850
Weight per piece (including packing)	187.4 g
Weight per piece (excluding packing)	185.5 g
Customs tariff number	96121010
Country of origin	US

# THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



## Technical data

### Product properties

Product type	Ink ribbon
Scope of supply	Ink ribbon
Marking	
Identification technology	Thermal transfer

### Dimensions

Width	64 mm
Length	300 m
Length of roll	300 m

### Material specifications

Color	black (RAL 9005)
Material	Polyolefin-compatible ink coating

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months after production date.

# THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



## Classifications

### ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

### ETIM

ETIM 9.0	EC001694
----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)