

# FLKM 50-PA/25/S7-1500 - Front adapter

1089346

<https://www.phoenixcontact.com/us/products/1089346>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for SIMATIC® S7-1500 digital 25 mm modules, 1x 32 channels can be connected. The front adapters are plugged into the front connectors on the I/O modules, and once plugged in they can no longer be separated.

## Commercial data

Item number	1089346
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C421
Product key	DK231S
GTIN	4055626891972
Weight per piece (including packing)	40 g
Weight per piece (excluding packing)	50 g
Customs tariff number	85366990
Country of origin	DE

# FLKM 50-PA/25/S7-1500 - Front adapter

1089346

<https://www.phoenixcontact.com/us/products/1089346>



## Technical data

### Product properties

Product type	Front adapter
Product family	VARIOFACE

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Oversupply category	II
Pollution degree	2

### Electrical properties

Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (per branch)	≤ 1 A
Current (per byte)	≤ 2 A

#### Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

#### Supported controller SIEMENS S7-1500

Suitable I/O card	6ES7521-1BL10-0AA0
	6ES7522-1BL10-0AA0
	6ES7523-1BL00-0AA0

## Connection data

### Connection 1 (control level)

Connection method	Plug-in connection
Number of connections	1
Number of positions	40

### Connection 2 (field level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

## Dimensions

### Item dimensions

Width	12.71 mm
Height	118.55 mm

# FLKM 50-PA/25/S7-1500 - Front adapter



1089346

<https://www.phoenixcontact.com/us/products/1089346>

Depth	27.75 mm
-------	----------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

UL, USA/Canada

Identification	UL 508 Recognized
----------------	-------------------

## Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	Plug-in mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM 50-PA/25/S7-1500 - Front adapter



1089346

<https://www.phoenixcontact.com/us/products/1089346>



## Drawings

Circuit diagram



# FLKM 50-PA/25/S7-1500 - Front adapter

1089346

<https://www.phoenixcontact.com/us/products/1089346>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1089346>



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

# FLKM 50-PA/25/S7-1500 - Front adapter

1089346

<https://www.phoenixcontact.com/us/products/1089346>



## Classifications

### ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

### ETIM

ETIM 9.0	EC002584
----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# FLKM 50-PA/25/S7-1500 - Front adapter

1089346

<https://www.phoenixcontact.com/us/products/1089346>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)