

FOC-C-SCD-SM-APC - FO connectors



1089516

<https://www.phoenixcontact.com/us/products/1089516>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

SC duplex single mode APC connector for wire or cable assembly



Product description

SC duplex connector, for assembling onto wires or cables with a diameter of 2.0 mm or 3.0 mm, single mode 9/125 µm APC. The reusable connector is particularly suitable for quick and easy field connection, as there is no need for bonding and polishing.

Your advantages

- Suitable for quick and easy field assembly or repair
- No bonding or polishing
- Reusable connectors
- A real alternative to splicing
- Optimum attenuation values with easy assembly
- Long-term durability thanks to the latest index matching gel
- The 8° fiber transition ensures optimum return attenuation (RL)

Commercial data

Item number	1089516
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAC
GTIN	4055626894409
Weight per piece (including packing)	13.6 g
Weight per piece (excluding packing)	13 g
Customs tariff number	85367000
Country of origin	DE

Technical data

Product properties

Product type	Fiber optic connector (cable side)
Type	SC
Number of positions	2
Connection profile	SC duplex plug
Number of slots	2
Cable outlet	straight

Electrical properties

Attenuation	≥ 0.5 dB 900 μ m (95%, <0.7 dB for cable connection)
-------------	---

Connection data

Connection method	mechanical splice
-------------------	-------------------

Dimensions

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Material	Plastic
Ferrule material	Zirconia ceramics
Housing material	PBT

Cable/line

Cable type	Single-mode fiberglass
Cable type	for all common cable types
Cable structure	STB and TB
External cable diameter	0.25 mm up to 3 mm (for the wire and cable connection) 2 mm ... 3 mm (Core assembly)
External sheath, color	green
Wire diameter	2 mm ... 3 mm
Individual wire diameter	900 μ m (for pigtails 0.9 mm, for cable connection 2 mm and 3 mm)
Tensile strength short-term/long-term	50 N
Halogen-free	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	Fiberglass
Fiber type	Single mode 9/125 μ m
Transmission medium	FO

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Mechanical data

Insertion/withdrawal cycles	≥ 500 (according to IEC 61300-2-2)
Extraction force per signal contact	≥ 50 N (Cable connection in accordance with IEC 61300-2-4)

Characteristics

Attenuation	≥ 0.5 dB 900 μm (95%, <0.7 dB for cable connection)
-------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (with cable connection only at room temperature)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Standards and regulations

Flame resistance	yes
------------------	-----

Mounting

cable layer type	Indoors
------------------	---------

FOC-C-SCD-SM-APC - FO connectors



1089516

<https://www.phoenixcontact.com/us/products/1089516>

Classifications

ECLASS

ECLASS-15.0	19170122
ECLASS-13.0	19170122

ETIM

ETIM 9.0	EC001122
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%