

# RTU READY 161408 - Control cabinet

1094594

<https://www.phoenixcontact.com/us/products/1094594>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prewired control cabinet with power supply, surge protective device, and circuit breaker for use with remote control and monitoring devices



## Product description

To simplify the selection and installation of wireless devices, Phoenix Contact offers the RTU READY... enclosure system to house radios, PLCs, or other control products. The prewired control cabinet provides a 24 V DC power supply and surge protection for line power and antenna connections, and terminal blocks for easy connectivity, all mounted on standard NS 35 mounting rail.

The selected components provide a robust housing with reliable power. Simply add a radio, antenna, or controller to complete the system.

## Your advantages

- Supply voltage: 24 V DC
- 100 V AC ... 240 V AC nominal input voltage range
- Prewired cabinetry with extra terminal blocks for simple, flexible installation
- UL 508A Listed
- COAXTRAB surge protection for antenna connection

## Commercial data

Item number	1094594
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DT02
Product key	DTHDCA
GTIN	4063151030704
Weight per piece (including packing)	1.05 g
Weight per piece (excluding packing)	1 g
Country of origin	US

# RTU READY 161408 - Control cabinet



1094594

<https://www.phoenixcontact.com/us/products/1094594>

Set consists of

UNO-PS/1AC/24DC/90W/C2LPS - Power supply

2902994

<https://www.phoenixcontact.com/us/products/2902994>

Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/90 W



## RTU READY UPS 161408 - Control cabinet

1094596

<https://www.phoenixcontact.com/us/products/1094596>

Prewired control cabinet with power supply, battery backup, surge protective device, and circuit breaker for use with remote control and monitoring devices



# RTU READY 161408 - Control cabinet

1094594

<https://www.phoenixcontact.com/us/products/1094594>



## Technical data

### Notes

#### Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

### Product properties

Product type

Control box

### Electrical properties

#### Supply

Supply voltage range

85 V AC ... 264 V AC

Typical current consumption

3.75 A

### Dimensions

Width

384 mm

Height

443 mm

Depth

221 mm

### Material specifications

Housing material

PC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)

-25 °C ... 70 °C

### Standards and regulations

#### Standards

Standards/regulations

UL 508A

# RTU READY 161408 - Control cabinet

1094594

<https://www.phoenixcontact.com/us/products/1094594>



## Classifications

### ECLASS

ECLASS-13.0

27370190

# RTU READY 161408 - Control cabinet

1094594

<https://www.phoenixcontact.com/us/products/1094594>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)