

ZB 16,LGS:L1-N,PE - Zack marker strip



0827462

<https://www.phoenixcontact.com/us/products/0827462>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, labeled, printed horizontally: L1, L2, L3, N, PE, mounting type: latching, for terminal block width: 16.3 mm, Number of individual labels: 5, text field height: 10.5 mm, text field width: 16.25 mm

Commercial data

Item number	0827462
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4046356431422
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.77 g
Customs tariff number	49119900
Country of origin	DE

ZB 16,LGS:L1-N,PE - Zack marker strip



0827462

<https://www.phoenixcontact.com/us/products/0827462>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	16.3 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	5
Printing direction	printed horizontally
Printing	L1, L2, L3, N, PE

Dimensions

Width	16.00 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	16.3 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb

ZB 16,LGS:L1-N,PE - Zack marker strip



0827462

<https://www.phoenixcontact.com/us/products/0827462>

Duration	96 h
Temperature for testing	120 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZB 16,LGS:L1-N,PE - Zack marker strip


0827462

<https://www.phoenixcontact.com/us/products/0827462>



Drawings

Schematic diagram



ZB 16,LGS:L1-N,PE - Zack marker strip



0827462

<https://www.phoenixcontact.com/us/products/0827462>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 16,LGS:L1-N,PE - Zack marker strip



0827462

<https://www.phoenixcontact.com/us/products/0827462>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.015 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com